



MATERIAL NUMBER	OLD PART NUMBER
130018-0210	41481



SCHEMATIC



VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	8 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PVC	YELLOW
2	CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
4	OVERMOLD	PVC	YELLOW

RLSD DRAWING EC NO: WNA2010-0131 DRWN: BWOODMAN 8/24/09 CH'KD: TW APPR: JFMURPHY 2009/08/27 A	DESCRIPTION REV	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ----	DESIGN UNITS ----	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY BW	DATE 2009/08/25	TITLE MC 5P FEMALE/MALE 90 ADAPTER ----					
			4 PLACES	±----	±----	CHECKED BY JM	DATE 2009/08/25						
			3 PLACES	±----	±----	APPROVED BY JFMURPHY		DATE 2009/08/26		molex	MOLEX INCORPORATED		
			2 PLACES	±----	±.01	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130018-002					
			1 PLACE	±0.3	±----								
			ANGULAR ±----°										
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									