

GNM1M2R71A473MA01#

“ # ” indicates a package specification code.

To be discontinued

General



125℃

Reflow OK

RoHS

< List of part numbers with package codes >
GNM1M2R71A473MA01D

Shape



L size	1.37 ± 0.15mm
W size	1.0 ± 0.15mm
T size	0.6 ± 0.1mm
Distance between external terminals P	0.64 ± 0.05mm
Size code in inch(mm)	0504 (1410)

References

Packaging	Specifications	Minimum quantity
D	180mm Paper taping	4000

Mass (typ.)	
1 piece	4.7mg
180mm Reel	137g

Specifications

Capacitance	47000pF ± 20%
Rated voltage	10Vdc
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 125
Operating temperature range	-55 to 125

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.