



CIRCUIT BOARD SUPPORTS ON BASE &
SELF THREADING CIRCUIT BOARD SUPPORTS

SCBSB

Adhesive Mount Male Stud Circuit Board Support





New

- #6-32 male thread is secured using Richco nylon hex nut item number HN-6-32-01. See page 813
- Adhesive: 1/32 (0.8) thick tape
- Material: UL94 V-2, Nylon 6/6
- Color: Natural

Item No.	"A" Standoff Height	Bulk Pack Qty.
SCBSB-4-01A-RT	1/4 (6.4)	1000
SCBSB-6-01A-RT	3/8 (9.5)	1000
SCBSB-8-01A-RT	1/2 (12.7)	1000
SCBSB-10-01A-RT	5/8 (15.9)	1000
SCBSB-12-01A-RT	3/4 (19.1)	1000
SCBSB-14-01A-RT	7/8 (22.2)	1000
SCBSB-16-01A-RT	1 (25.4)	1000
SCBSB-18-01A-RT	1 1/8 (28.6)	1000

PSB

Push Spacer on Adhesive Base




Specifications:

- Material: Nylon 6/6
- Color: Natural
- Adhesive backing: Double-sided adhesive tape with release tab

Item No.	UL94 V-2	UL94 V-0	A In	mm	Bulk Pack Qty.
PSB-6M-01A2-RT	PSB-6M-19A2-RT	0.236	6.0	1000	
PSB-8 M-01A2-RT	PSB-8 M-19A2-RT	0.314	8.0	1000	
PSB-10M-01A2-RT	PSB-10M-19A2-RT	0.393	10.0	1000	
PSB-12M-01A2-RT	PSB-12M-19A2-RT	0.472	12.0	1000	
PSB-14M-01A2-RT	PSB-14M-19A2-RT	0.551	14.0	1000	
PSB-16M-01A2-RT	PSB-16M-19A2-RT	0.629	16.0	1000	

PSBM

Adhesive Mount Push Spacer





- Smaller size takes up less real estate on the board
- Adhesive: 1/32 (0.8) thick tape
- Material: Nylon 6/6
- Color: Natural

Item No.	UL94 V-2	UL94 V-0	"A" Standoff Height	Bulk Pack Qty.
PSBM-3-01A-RT	PSBM-3-19A-RT	.189 (4.8)	1000	
PSBM-4-01A-RT	PSBM-4-19A-RT	.252 (6.4)	1000	
PSBM-5-01A-RT	PSBM-5-19A-RT	.311 (7.9)	1000	
PSBM-6-01A-RT	PSBM-6-19A-RT	.374 (9.5)	1000	
PSBM-7-01A-RT	PSBM-7-19A-RT	.437 (11.1)	1000	
PSBM-8-01A-RT	PSBM-8-19A-RT	.500 (12.7)	1000	
PSBM-9-01A-RT	PSBM-9-19A-RT	.563 (14.3)	1000	
PSBM-10-01A-RT	PSBM-10-19A-RT	.626 (15.9)	1000	
PSBM-12-01A-RT	PSBM-12-19A-RT	.752 (19.1)	1000	
PSBM-14-01A-RT	PSBM-14-19A-RT	.874 (22.2)	1000	

SCBSST

Circuit Board Support, Self-Threading





- The threaded hole acts as a die and threads the bottom end when screwed in
- Can be used in either a #8 or M4 threaded hole
- Easily installed by hand with minimal force
- Material: UL94 V-2 Nylon 6/6
- Color: Natural

Item No.	"A" Standoff Height	Bulk Pack Qty.
SCBSST-4-01	1/4 (6.4)	1000
SCBSST-6-01	3/8 (9.5)	1000
SCBSST-8-01	1/2 (12.7)	1000
SCBSST-10-01	5/8 (15.9)	1000
SCBSST-12-01	3/4 (19.1)	1000
SCBSST-14-01	7/8 (22.2)	1000
SCBSST-16-01	1 (25.4)	1000
SCBSST-18-01	1-1/8 (28.6)	1000
SCBSST-22.5-01	1-13/32 (35.7)	1000

MSPMST

Micro Self-Threading Mini Support Post



Specifications:

- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94 V-2

Features:

- Self-threading into #4 or M3 threaded hole

Item No.	A In	mm	Bulk Pack Qty.
MSPMST-2-01	0.125	3.2	1000
MSPMST-3-01	0.188	4.8	1000
MSPMST-4-01	0.250	6.4	1000
MSPMST-5-01	0.313	7.9	1000
MSPMST-6-01	0.375	9.5	1000
MSPMST-7-01	0.438	11.1	1000
MSPMST-8-01	0.500	12.7	1000
MSPMST-9-01	0.563	14.3	1000
MSPMST-10-01	0.625	15.9	1000