

3. TOLERANCES NON-ACCUMULATIVE.



4 PACKAGED IN HARD TRAY.

5 FINISH; CONTACT AREA: 0.00025 MIN GOLD PLATE ON
0.001 MIN ALL OVER NICKEL
SOLDERING AREA: BRIGHT TIN LEAD PLATE.


6 PART PACKAGED PER EIA-18704 STANDARD. REEL
DIAMETER SHALL BE 330mm, TAPE WIDTH SHALL BE
88mm, AND TAPE PITCH SHALL BE 36mm.

7 LATCH PLATING: TIN-LEAD FOR P/N: 8-390112-1 ONLY
(IDENTICAL TO PREVIOUS P/N: 390112-1)

8 DATE CODE (4-DIGITS), LOCATED AS SHOWN.
TO BE INTERPRETED AS FOLLOWS:
DIGIT # 1 - LAST DIGIT OF YEAR.
DIGITS # 2 AND # 3 - CALENDAR WEEK.
DIGIT # 4 - DAY OF THE WEEK
(WITH SUNDAYS AS DAY 1).



SECTION X-X
ROTATED 90° CCW
SCALE 8:1



SECTION Y - Y
ROTATED 90° CCW
SCALE 8:1

NIL	AVAILABLE	NATURAL		144	8-390112-1
NIL	AVAILABLE	BLACK		144	7-390112-1
NIL	AVAILABLE	NATURAL		144	6-390112-1 
3-390112-1	NOT AVAILABLE	NATURAL		144	3-390112-4 
NIL	AVAILABLE	NATURAL		144	3-390112-1 
390112-1	NOT AVAILABLE	NATURAL		144	390112-4
NIL	AVAILABLE	NATURAL		144	390112-1
SUPERSEDED BY	REMARKS	COLOR	FINISH	POS	PART NO.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN W. SORAH 6-23-97		TE Connectivity	
mm				CHK ALAN ANG 01-21-02			
		P L C .00 ±		NAME S.O. DIMM SOCKET ASSY, 0.8mm, 3.3V, 144 POSITION, HIGH PROFILE FOR SDRAM TYPE MODULE			
		P L C .00 ±		REV SF LEONG			
		P L C .00 ±		PRODUCT SPEC 108-1739			
ANGLES		P L C .00 ±		APPLICATION SPEC 114-1114			
FINISH		P L C .00 ±		SIZE A1		CASE CODE 00779	
MATERIAL		P L C .00 ±		DRAWING NO C=390112		RESTRICTED TO -	
		WEIGHT -		SCALE 4:1		SHEET 1 of 2	
SEE TABLE		CUSTOMER DRAWING		REV R1			



DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		DWG. NO. W_SORAH 6-23-91 CHK. ALAN ANG 1-21-02 DES. SE LEONG		 TE Connectivity	
mm		0 P.LC ± .002 1 P.LC ± .002 2 P.LC ± .002 3 P.LC ± .002 4 P.LC ± .002 ANGLES ± .002 FINISH ± .002		NAME S.O. DIMM SOCKET ASSY, 0.8mm, 3.3V, 144 POSITION, HIGH PROFILE FOR SDRAM TYPE MODULE PRODUCT SPEC 108-11739 APPLICATION SPEC 114-1114		SIZE A1 CASE CODE 00779 DRAWING NO. C390112	
MATERIAL 		SEE TABLE		WEIGHT -		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1 SHEET 2 OF 2 REV R1			