







SEE NOTE 2.



3.SUGGESTED TORQUE IS 3.0 IN-LBS min.



(PANEL THICKNESS 0.76–1.02 MM)

[illegible]

Tous droits réservés. Reproduction ou communication à des tiers sans autorisation écrite de FRAMATOMEGROUP.
All rights reserved. Reproduction or communication to third parties is only for authorized use without written permission of FRAMATOMEGROUP.
Copyright © FRAMATOMEGROUP

Tous droits réservés. Reproduction ou communication à des tiers sans autorisation écrite de FRAMATOMEGROUP.
All rights reserved. Reproduction or communication to third parties is only for authorized use without written permission of FRAMATOMEGROUP.
Copyright © FRAMATOMEGROUP

PRODUCT NO.
52520-XXXX29
52520-XXXX24

NOTE 1.

ORDERING DATA:

52520-X X X X 29

- PIN NUMBER
- TAIL-GUIDE POST
1 - WITH POST
- COLOR OF HOUSING AND TAIL-GUIDE
0- BLACK
1- NATURAL
- MOUNTING SCREW
0 - WITHOUT MOUNTING SCREW
1 - WITH MOUNTING SCREW (UNASSEMBLED)
- CONTACT PLATING
0 - GOLD FLASH
1 - 15 u" Au
2 - 30 u" Au

NOTE 2.

ORDERING DATA:

52520-X X X X 24

- PIN NUMBER
- TAIL-GUIDE POST
1 - WITH POST
- COLOR OF HOUSING AND TAIL-GUIDE
0- BLACK
1- NATURAL
- MOUNTING SCREW
0 - WITHOUT MOUNTING SCREW
1 - WITH MOUNTING SCREW (UNASSEMBLED)
- CONTACT PLATING
0 - GOLD FLASH
1 - 15 u" Au
2 - 30 u" Au

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 FRAMATOMEGROUP			
ltr	ecn no	dr	date	linear	0.0±	projection		title RECEPTACLE OF DVI R/A TYPE			
B					0.00±						
					0.000±						
				angles	0°±		MM/INCH	product family DVI size dwg no A3 52520			
				dr	Benny Chen 01/13/00						
				enr	Benny Chen 01/13/00						
				chr	Paul Wang 01/13/00						
				appd	Paul Wang 01/13/00						
sheet index		revision sheet									