

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [120066-0271](#)
Status: **Active**
Overview: [Brad® Micro-Change® \(M12\) Connectors](#)
Description: Micro-Change® (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 22 AWG, PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120066](#)
Connector End A Micro-Change® (M12)
Connector End B Micro-Change® (M12)
IP Rating IP67
Overview [Brad® Micro-Change® \(M12\) Connectors](#)
Product Name Micro-Change® (M12)
Type Double Ended
UPC 78678824184

Physical

Cable Diameter 5.33mm (.210")
Cable Length 2.0m (6.56')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Contact Copper Alloy
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Viton
Material - Plating Mating Gold over Nickel
Net Weight 98.000/g
Orientation Straight
Poles 4
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 22
Wire/Cable Type UL 2661

Electrical

Current - Maximum per Contact 4A
Voltage - Maximum 250V AC/DC

Material Info

Old Part Number 884030A09M020

Reference - Drawing Numbers

Sales Drawing SD-120066-005



image - Reference only

Series

EU RoHS

**RoHS Compliant by
Exemption**
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[120066Series](#)

This document was generated on 01/30/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION