



OAB800AN Series



AC Blower, ball bearing
125x126x39mm (4.9"x 5"x 1.5")



Side Inlet Blower

Frame & Impeller

Aluminum die-cast shell with UL94V-0 impeller

Connection

Lead Wires

Motor

Shaded pole, inner rotor, single phase, impedance protected

Bearing System


Dual ball - sealed

Operating Temp: Ambient non-condensing allowable thermal range -20C~+75C

-L10 Life: MTBF life test 85,000 hours at +45C, 40,000 hours at +60C

-Dielectric Strength: Over 1 min. at 1,500 VAC, 0.5mA, 50/60 Hz

-Insulation Resistance: Over 100 Mega Ohm at DC 500V



Model Number	OAB800AN-11-1B	OAB800AN-22-1B
Part Number	263311000	263611000
Nominal Voltage	115 VAC	220 VAC
Voltage Range	80 ~ 120	150 ~ 240
Rated Power	18 W	18 W
Rated Speed (RPM)	2800	2800
Airflow (CFM)	30	30
Noise Level (dB)	48	48
Max. Static Pressure	0.51 "H2O	0.51 "H2O