

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION, 19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				G	REV PER 0G3A-0031-99	080CT99	JR/TM


AMP
WIRE RANGE

1/0 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 1.78±0.08 [.070±.003]
FOR 14.73 [.580] MAX WIRE INS DIA



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°c

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
42.4-60.6mm² [83,700-119,500]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MS25036-132 CLASS2	-	LOOSE PC	324056	
MILITARY P/N AND CLASS	QTY	PACKAGE TYPE	PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -	DR 6-18-93 S.S. GOULDEN	 AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 6-18-93 R. HERSEY			
	APPD 6-18-93 B. BARE	NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 1/0 AWG		
	APPD 6-18-93 M. ELLIS			
PRODUCT SPEC -				
MATERIAL COPPER PER ASTM B-152 NYLON (MIL-M-20693) TYPE 1 COLOR: BLUE	APPLICATION SPEC -	SIZE B	CAGE CODE 00779	DRAWING NO C-324056
FINISH TIN PLATE PER MIL-T-10727	WEIGHT -	SCALE NTS	SHEET 1 OF 1	