

Search Results

- Evaluate
  - FAQ's
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'F6PE10T-NM8'**

Your search criteria matched only one product, shown below

**F6PE10T-NM8**



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes Opti-Core® Patch Cords and Pigtails, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs) and Mini-Com® Adapter Modules
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

*Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.*

*Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.*

• Part Number	F6PE10T-NM8
• RoHS Compliancy Status	Compliant
• Note	Intended for use in fixed installations which are outside the scope of RoHS.
• Part Description	Keyed LC (Keyed T-steel blue) to multimode duplex plenum pigtail, 1.6mm jacketed cable (one duplex keyed LC connector on one end and open on the other end) - 62.5/125µm.
• Product Type	Keyed LC Patch Cords
• Length (m)	8
• Fiber Compatibility	62.5/125µm
• Fiber Cable Size	1.6mm
• Fiber Cable Type	Jacketed
• Fiber Type	Multimode 62.5/125
• Cable Type	Duplex
• Connector 1 Type	LC Connector Keyed T (Steel Blue)
• Connector 2 Type	Pigtail
• Flammability Rating	Plenum (OFNP)
• Key Type and Color	Keyed T (Steel Blue)
• No. of Fibers	2
• Pricing Description	Keyed LC (T-Steel Blue) to pigtails, 62.5µm Duplex, Patch Cord 8M
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.