



- NOTE:
- 1 HOUSING: GLASS FILLED THERMOPLASTIC
CONTACTS: COPPER ALLOY
 - 2 PLATING:
CONTACT AREA: PERFORMANCE LEVEL 2 ACC. TO DIN 41612
SOLDERING AREA: TIN OVER NICKEL
 - 3 CONTACT ARRANGEMENTS:
AN ASTERISK "X" DENOTES A SIGNAL CONTACT.
AN ASTERISK "⊗" DENOTES KINKED A SIGNAL CONTACT.
 - 4 KINKED POSTS
- 5. SOLDER POSTS SUITABLE FOR 1,0 NOM. P.C.B. HOLES
 - 6. CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE



ROW	POS	
	a	1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 31 32
	b	
	c	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH

-

DWN: RAVINDRA K, 15MAR11

CHK: MARCIN KOMAR, 07APR11

APVD: STEFFAN HABERSTROH, 07APR11

PRODUCT SPEC

APPLICATION SPEC

WEIGHT: -

CUSTOMER DRAWING

WITH: 2, 4

FINISH

MATERIAL: 1

2173047-4

TE PARTNUMBER

TE Connectivity

NAME: 96P.IEC-C FEM.CONN.
ACC. DIN 41612 WITH SOLDER POSTS
2,4 - 3,2mm P.C.BOARD THICKNESS

SIZE: A2

CAGE CODE: 00779

DRAWING NO: C=2173047

RESTRICTED TO: -

SCALE: NTS

SHEET: 1 OF 1

REV: A