


METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP		E13288 Listed
WIRE RANGE		
4 AWG	4 AWG	
SOLID OR STRANDED	STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS
4 AWG	NOT APPLICABLE	
SOLID OR STRANDED		

△ STAMP AMP 4* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ±
3 PLC DEC ±
ANGLES

DR 9/9/93
DK SCHRUM
CHK 9/10/93
DA PATTERSON
APPD 9/10/93
CH KULYNICH

AMP Incorporated
Harrisburg, PA 17105-3608

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752

VOLTAGE RATING:
NOT APPLICABLE

MATERIAL
COPPER PER
ASTM B-152
ANNEALED

APPD 9/10/93
JL MECKLEY
PRODUCT SPEC

NAME
TERMINAL, RING TONGUE,
SOLISTRAND™

FOR APPLICATION
TOOLING INFORMATION
1-800-722-1111

WIRE CROSS SECTIONAL AREA RANGE:
16.8-26.7mm² [33.100-52.600] CIR MILS
SOLID OR STRANDED

FINISH
TIN PLATE
0.00254 [1.000100] MIN
THK PER MIL-T-10727

APPLICATION SPEC

SIZE
CAGE CODE
00779
DRAWING NO
55951