

YTS, YTQ SERIES


HIGH-DENSITY SOCKET STRIP

Mates with:
YTT, YTW, YTE, TMMS

Yes

YTS Lead-Free Solderable:
Wave Only
YTQ Lead-Free Solderable:
Wave or reflow with
Matte Sn plating

RU[®]
FILE NO. E111594



TYPE SOCKET

YTS
= Flat Tail
(Style -01 only)

YTQ
= Square Tail

1

NO. PINS PER ROW

02 thru 50

LEAD STYLE

Specify LEAD STYLE from chart

PLATING OPTION

-L
= 10 μ" (0.25 μm)
Gold contact, Matte Tin on tail

-F
= Gold flash on contact, Matte Tin on tail

ROW OPTION

-Q
= Four Row

-5
= Five Row

-6
= Six Row

OTHER OPTION

- "XXX"
= Polarized Position (Indicate position number)

LEAD STYLE	A
-01	(2.29) .090
-02	(15.24) .600
-03	(5.28) .208

TYPE SOCKET	B
YTS	(0.25) (0.51) .010 x .020
YTQ	(0.51) .020 SQ

-Q

-5

-6

Note:
Some lengths, styles and options are non-standard, non-returnable.