



A620

Pressure Adapter



Measurement Range

1 to 500 psi
1 to 30 inHg

Accuracy

$\pm$ (1% of reading, + 0.3 psi)
 $\pm$ (1% of reading, + 0.5 inHg)

Adapter Output

1mVDC per 1 psi
1mVDC per 1 inHg

General Specifications

Input Connection: 1/4" NPT
Lead Length: 78" (2m)
Output Connection Type: Dual banana plug

Use This Adapter With

Most TPI brand and any competitor DMM, clamp-on or oscilloscope having the capability of measuring up to 2000mV AC/DC (2V AC/DC), 10M Ohm input impedance, and equipped with industry standard spaced input jacks 19mm on center.

Copyright © 2007 Test Products International, Inc.