




General ordering data

Version	EXI enclosure, 90 mm, 160 mm, 360 mm, glass fibre-reinforced polyester
Order No.	9510270000
Part designation	Klippon POK 7 Ex
EAN	4008190498610
Qty	1

Dimensions

Fixing dimension, height	110 mm
Fixing dimension, width	340 mm
Length	160 mm
Height	90 mm
Width	360 mm

General details

Sealing material	Polyurethane und chloroprene
Enclosure fixing	Holes 6 mm
Cover fixing	4 stainless steel M6 screws
Colour	grey
Class of protection to EN 60529	IP 66
Weight	2150 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	130 °C

Screwed cable glands top/bottom

M 40	5
M 20	20
M 25	8
M 12	45
M 16	36
M 32	6
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M32	2
M12	11
M40	1
M16	6
M20	4
M25	2
Side of enclosure	left / right

Classifications

ETIM 2.0	EC000520
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Related products

Length	Height	Width
160 mm	90 mm	360 mm