



REV.	DATE	DESCRIPTION
NC	06/14/00	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE				
1 BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	DRAWN G.R.S.	06/14/00				
2 INSULATOR	TEFLON	NATURAL		CHECKED		TITLE SMB BULKHEAD CRIMP JACK (FOR RG-179/U CABLE- 75ohm)			
3 CONTACT PIN	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	ISSUED					
4 FERRULE	COPPER	NICKEL				SIZE A	FSCM NO. 99001	DWG. NO. 142109.DWG	REV. NC
5 LOCK WASHER	BRASS	NICKEL							
6 HEX NUT	BRASS	NICKEL							
7									
8			DO NOT SCALE DRAWING			SCALE NA	PART NO. 142109	SHEET 1 OF 1	