







REV.	DATE	DESCRIPTION
A	01/25/04	UPDATE DRAWING FORMAT
B	08/07/05	MODIFY CONTACT PIN



NOTE:

1. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
8						DRAWN	G.R.S.							08/07/05		
7						CHECKED										
6	SOLDER BARREL	BRASS	GOLD	1			ISSUED		PART DESCRIPTION							
5	INSULATOR	TEFLON	NATURAL	1			SHEET	1 OF 1	SMA DIRECT SOLDER JACK (FOR .047” SIMI-RIGID CABLE)							
4	CONTACT PIN	BER. COPPER	GOLD	1					PART NO.		132257					
3	INSULATOR	TEFLON	NATURAL	1		CAD FILE		DWG. NO.		132257.DWG	REV.	B	SIZE	A	SCALE	NA
2	BODY	BRASS	GOLD	1		C:/132/132257.DWG										
1	DESCRIPTION	MATERIAL	FINISH	QTY												