


NYLON 6/6 (RMS-01) COLOR: NATURAL PART NO.	UV STABILIZED (RMS-46) COLOR: BLACK PART NO.	MAX. BUNDLE DIA.	LENGTH "L" APPROX.	NYLON 6/6 FLAME RET. (RMS-75), UL94-V0 COLOR: NATURAL TO ORDER ADD "-V0" TO P/N	NYLON 4/6 (RMS-109) HI TEMPERATURE COLOR: NATURAL TO ORDER ADD "-HT" TO P/N (NOTE 3.)	NYLON 6/6 (RMS-73) LOW TEMPERATURE COLOR: BLACK TO ORDER ADD "-ST" TO P/N	NYLON 6/6 HEAT STABILIZED (RMS-47) UL 94-V2 COLOR: BLACK TO ORDER ADD "-HS" TO P/N	COLOR (NOTE 2.)
WIT-50S	WIT-50S-UVB	1-1/2 (38.1)	6.0 (152.4)	SPECIAL	SPECIAL	SPECIAL	SPECIAL	SPECIAL
WIT-50R	WIT-50R-UVB	2 (50.8)	8.0 (203.2)	STANDARD	STANDARD			STANDARD
WIT-50L	WIT-50L-UVB	4-1/2 (114.3)	15.40 (391.2)	SPECIAL	N/A		STANDARD	SPECIAL

NOTES:
1. MIN. LOOP TENSILE: 50 lbs

2. COLOR: RED (-RD),
TO ORDER, ADD COLOR SUFFIX TO PART NO.

COLORS: GREEN (-GN), BLUE (-BL), YELLOW (-YL), NEON-GREEN (-NGN),
NEON-YELLOW (-NYL), NEON-PINK (-NPK)
AND NEON-ORANGE (-NOR), AVAILABLE BY SPECIAL ORDER ONLY

3. PARTS ARE SERVICEABLE UP TO 150°C



I	SEE CO 200134 FOR CHANGES	SK 02.28.08
H	SEE CO 200035 FOR CHANGES	SK 09.26.07
G	SEE ECN #862 FOR CHANGES	SM 10.04.04
F	SEE ECN #724 FOR CHANGES	SM 11.07.03
E	ADDED MAT'L INFO TO TABLE AND NOTES PER CATALOG	SM 05.06.02
D	UPDATED TABLE AND MAT'L NOTES	SM 04.23.02
C	CHANGED FILE NO.	SM 04.01.02
B	DIM. "L" FOR WIT-50L CHANGED TO 15.4	J.L. 05.01.00
A	MAT'L RMS-46 ADDED	J.L. 06.03.98
REV	DESCRIPTION	ENGR DATE

TITLE: WIT-50 SERIES					
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # WIT-50X	DWN: P.B.	APP:	FINAL	
	MAT'L: SEE NOTES & TABLE	DT: 08-09-95	DT:	PART #	
	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060		SEE TABLE	