

## Item # ATV312H037M3, Variable Speed Drive



### Variable Speed Drive

Variable Speed Drive

## SPECIFICATIONS

|                      |                 |
|----------------------|-----------------|
| Family               | Altivar 312     |
| Product Line         | AC Drives       |
| Output Ampere Rating | 3.3             |
| Application          | Constant Torque |
| Enclosure Rating     | IP20            |
| Frame Size           | 1               |
| HP Rating            | 0.5             |
| kW Rating            | 0.37            |
| Voltage Rating       | 208/240VAC      |
| Input Phase          | 3 Phase         |
| Output Phase         | 3 Phase         |
| Control Voltage      | 24Vdc           |
| Logic Input          | 6               |
| Analog Input         | 3               |

|                     |                              |
|---------------------|------------------------------|
| Analog Output       | 1                            |
| Logic/Relay Outputs | 1 Form C, 1 NO               |
| Weight [lb]         | 1.98                         |
| Weight [kg]         | 0.90                         |
| UL File No.         | E116875                      |
| CSA File            | 1464725                      |
| Other               | CE, GOST, RoHS, NOM, EMITECH |
| Communication       | Modbus and CANopen           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV312H037M3](#)