

KWIK SNAP Terminal Blocks

Specification:-

Housing: Polypropylene (94-V2 grade)
Metal Part: Plated Metal Insert
Tml Screw Zinc-plated steel

Features & Benefits:-

Easy, Kwik & clean break – No tools required
Pole dividers support screws for assembly
VDE approved & rated to T85-110
Formed, zinc plated steel insert

Hylec-APL Part Number

HYKS-02412PP

HYKS-03212PP

HYKS-05712PP

HYKS-07612PP

T04

T06

T10

T16

Voltage (V)

450

450

450

750

Ampere (A)

24

32

57

76

VDE / IEC-rated

Max Wiring Capacity (mm²)

4.0

6.0

10.0

16.0

Ambient Temperature : T85-T110°C

Dimensions (mm)

T04

T06

T10

T16

Height

12.2

14.0

16.3

20.9

Length

93.5

116.5

139.3

169.5

Width

17.8

20.0

23.4

27.7

Spacing

8.0

10.0

12.0

14.5



- Comply with IEC/EN60998-1,60998-2-1

- Colour: white




Tel :-

01933 234400

Fax :-

01933 234411



Web :- www.hylec-apl.com

Email :- sales@hylec-apl.com

Making The **Right** Connections