

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

SFW7R-3STE5

SFW7R-3STE5

SFW7R-3STE5 - FPC/FPC : SFW-R series, 7 Pos, Down Side Contact, Side Entry Surface Mount ZIF Connector, 1 mm (0.039 in.), non-Lead Free, with Cable Lock, Plastic Reel



Customer drawing



Product Environmental Compliance Report

MATURE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications

Download document

General Electrical Mechanical Physical Approvals / Certifications Mounting Other Features

General	
Cable Insertion	ZIF
Cable Lock	No
Contact location	Lower
Number of contacts	7
Orientation	Right Angle
Product Series	SFW-R
Electrical	
Withstanding Voltage	500V AC for 1 minute
Current rating	1A AC/DC
Resistance (Contact)	30 milli ohms max.
Resistance (Insulation)	500 M-ohms min.
Voltage rating	100V AC/DC
Mechanical	
Durability (Mating cycles)	20 Cycles
Physical	
Cable Type	FPC/FPC
Material (Contact)	Phosphor Bronze, Tin Plated
Material (Housing)	Glass Reinforced PPS, UL94 V-0
Material (Slider)	Glass Reinforced PPS, UL94 V-0
Temperature (Operating - range)	-55°C to +85°C
Approvals / Certifications	
Damp Heat per JIS C 0022	Contact Resistance 50 milli ohms max., Insulation Resistance 100 M-ohms min.
Salt Spray per JIS C 0023	Contact Resistance 50 milli ohms max.
Temperature Cycling per JIS C 0025	Contact Resistance 50 milli ohms max.
Vibration per JIS C 0040	No discontinuity > 1 µ second
Mounting	
Mounting style (Board)	Surface Mount
Other Features	
Packaging (Type)	Embossed Tape on Reel

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.