



**Materials and Finish**

Body: PBT Thermoplastic,  
30% glass filled,  
UL94V-0 rated,  
black color

Contact Material: Phosphor Bronze,  
3 to 6 u" Gold Plated

**Electrical Specifications**

Contact Current Rating:  
3 Amp max.

Contact Resistance:  
10 milliohms max.

Dielectric Withstanding Voltage:  
AC 650 Volts RMS

Insulation Resistance:  
1000 Megohms min.

Temperature Rating:  
-55°C to +125°C

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS
A	5/5/98	New Drawing	C. Leiva		mm
B	5/6/98	Rev Plating	CHECKED BY	APPROVED BY	DATE
					5/5/98

S4040

Multiple Position Shunt

4 Position, 2.54 mm Pitch



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[S4040](#)