

Heyco® Lockit™ Nylon Cable Clamps

Lock onto Wire and Cable for Faster Final Assembly

Heavy Duty - 1/2" (12,7 mm) Wide, .06" (1,5 mm) Thick

MOUNTING HOLE DIAMETER		SCREW SIZE	PART DIMENSION A		PART NO.		DESCRIPTION
in.	mm.		in.	mm.	Black	Natural	


Push Lock Style For Panels up to .125" (3,2 mm) thick

NEW!	.187	4,7	Push Mount	1.00	25,4	3727	3727N	PLCC 1000
				1.13	28,6	3730	3731	PLCC 1125
				1.19	30,1	3734	3735	PLCC 1187
				1.25	31,8	3738	3739	PLCC 1250
				1.38	34,9	3742	3743	PLCC 1375
				1.50	38,1	3746	3747	PLCC 1500

Snap Lock Style

NEW!	.190	4,8	#10	1.00	25,4	3725	3726	SLCC 1000
				1.13	28,6	3728	3729	SLCC 1125
				1.19	30,1	3732	3733	SLCC 1187
				1.25	31,8	3736	3737	SLCC 1250
				1.38	34,9	3740	3741	SLCC 1375
				1.50	38,1	3744	3745	SLCC 1500

Standard colors black and natural.



Material	Nylon 6/6
Flammability Rating	94V-2
Temperature Range	32°F (0°C) to 221°F (105°C) - Black 32°F (0°C) to 185°F (85°C) - Natural

Snap Rivet Table - for use with Heyco® Nylon Cable Clamps

For our complete line of Snap Rivets, see pages 7-74 & 7-75

PANEL THICKNESS				PART NO.			DESCRIPTION
Minimum		Maximum		Black	White	V-0 Black	
in.	mm.	in.	mm.				

For .170" (4,3 mm) Mounting Hole, Light Duty Cable Clamps

.08	2,0	.12	3,0	9062	9063	9062F	PR 161-177
.12	3,0	.16	4,1	9064	9065	9064F	PR 161-217
.16	4,1	.20	5,1	9066	9067	9066F	PR 161-256
.20	5,1	.24	6,1	9068	9069	9068F	PR 161-295
.25	6,4	.31	7,9	9318	9319	9318F	PR 161-354
.39	9,9	.45	11,4	9320	9321	9320F	PR 161-492

For .203" (5,2 mm) Mounting Hole, Light or Heavy Duty Cable Clamps

.06	1,5	.10	2,5	9076	9077	9076F	PR 201-177
.10	2,5	.14	3,6	9078	9079	9078F	PR 201-217
.14	3,6	.18	4,6	9080	9081	9080F	PR 201-256
.18	4,6	.22	5,6	9082	9083	9082F	PR 201-295



Push Lock Style

- Push-in "arrowhead" locks part onto cable quickly and easily, for faster final assembly requiring **no additional hardware**.
- Resist corrosion, salt water, weak acids, grease, and common solvents.

Snap Lock Style

- Locking feature allows for preassembly onto cable quickly and easily, for faster final assembly.
- Lock securely but can be **removed and reused**.
- Resist corrosion, salt water, weak acids, grease, and common solvents.
- Standard Material Nylon 6/6. 94V-0 available. Consult Heyco.

Quick Specs



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[12078](#) [12081](#) [12068](#) [12084](#) [12071](#) [12076](#) [12074](#) [12079](#) [12067](#) [12082](#) [12072](#) [12075](#) [12083](#) [12069](#) [12077](#)
[12080](#) [12070](#) [12073](#)