


**T-1 Wire Terminal (standard)**


| Part Number | Design Voltage | Amps | MSCP | Life Hours | Filament Type |
|-------------|----------------|------|------|------------|---------------|
| CM8798      | 1.25           | .012 | .004 | 1,000      | C-6           |
| CM8910      | 1.35           | .220 | .020 | 25,000     | C-2R          |
| CM7201      | 1.50           | .015 | .010 | 5,000      | C-2R          |
| CM7202      | 1.50           | .066 | .015 | 100,000    | C-2R          |
| CM7203      | 1.50           | .075 | .030 | 16,000     | C-2R          |
| CM7018      | 2.50           | .320 | .210 | 10,000     | C-2R          |
| CM8601      | 2.50           | .015 | .001 | 10,000     | C-2R          |
| CM8711      | 2.50           | .320 | .210 | 5,000      | C-2R          |
| CM8732      | 2.50           | .100 | .100 | 10,000     | C-2R          |
| CM2128      | 3.0            | .013 | .001 | 10,000     | C-2R          |
| CM7205      | 3.0            | .015 | .020 | 5,000      | C-2R          |
| CM7206      | 3.0            | .024 | .020 | 10,000     | C-2F          |
| CM7207      | 3.0            | .060 | .030 | 100,000    | C-2R          |
| CM7208      | 3.0            | .120 | .150 | 16,000     | C-2R          |
| CM8846      | 3.0            | .008 | .001 | 16,000     | C-2R          |
| CM680       | 5.0            | .060 | .030 | 60,000     | C-2R          |
| CM683       | 5.0            | .060 | .050 | 25,000     | C-2R          |
| CM713       | 5.0            | .075 | .090 | 25,000     | C-2R          |
| CM715       | 5.0            | .115 | .150 | 40,000     | C-2R          |
| CM3022      | 5.0            | .021 | .030 | 10,000     | C-2R          |
| CM3211      | 5.0            | .115 | .200 | 5,000      | C-2R          |
| CM6022      | 5.0            | .021 | .030 | 10,000     | C-2R          |
| CM6150      | 5.0            | .060 | .150 | 5,000      | C-2R          |
| CM6212      | 5.0            | .080 | .150 | 15,000     | C-2R          |
| CM6801      | 5.0            | .060 | .030 | 100,000    | C-2R          |
| CM6830      | 5.0            | .060 | .050 | 25,000     | C-2R          |
| CM6831      | 5.0            | .060 | .050 | 25,000     | C-2R          |
| CM7007      | 5.0            | .064 | .080 | 40,000     | C-2R          |
| CM7008      | 5.0            | .064 | .080 | 40,000     | C-2R          |
| CM7019      | 5.0            | .015 | .010 | 10,000     | C-2V          |
| CM7131      | 5.0            | .075 | .090 | 25,000     | C-2R          |
| CM7151      | 5.0            | .115 | .150 | 40,000     | C-2R          |
| CM7209      | 5.0            | .015 | .020 | 10,000     | C-2F          |
| CM7210      | 5.0            | .030 | .030 | 16,000     | C-2F          |
| CM7211      | 5.0            | .080 | .150 | 15,000     | C-2R          |
| CM7212      | 5.0            | .115 | .200 | 5,000      | C-2R          |
| CM7213      | 5.0            | .115 | .200 | 5,000      | C-2R          |