

FJ-20-D-06.50-4

FJ-05-D-04.80-2

(1,00 mm) .0394"

FJ SERIES

FLAT FLEXIBLE CABLE (FFC) JUMPER

SPECIFICATIONS

For complete specifications
see www.samtec.com/FJ

Conductor:

Tin Plated Copper

Conductor

Resistance:

300 Ω/km max

Insulation Resistance:

10 MΩ/km min

(conductor-to-conductor)

Dielectric Test:

400 VAC during 1 minute

(conductor-to-conductor)

Temperature Rating:

-30°C to +80°C

Voltage Rating:

300 VAC

Flame Resistance:

VW-1 (UL 758)

RoHS Compliant:

Yes

Mates with:


FC1, ZF1

Double or
reversed ended

Variety of
pin counts

Variable
lengths

FJ	NO. OF POSITIONS	STYLE	OVERALL LENGTH	STRIP LENGTH
	-05, -10, -15, -20, -25, -30	-D = Double End -R = Reversed End	-“XX.XX” = Specify OVERALL LENGTH in inches (±1/8 inch) (-D = (50,80 mm) 2.00" minimum)	-2 = (2,00 mm) .079" -4 = (4,00 mm) .157" (Required for mating with FC1 & ZF1)



STRIP LENGTH	C
-2	(2,00) .079
-4	(4,00) .157

Note: Stiffener color will be blue or black at Samtec's discretion.

Note: Some sizes, styles and options are non-standard, non-returnable.