



## SOLDERING IRONS [LIGHT/HEAVY DUTY]



### LIGHT-SERIES

#### 9000 SERIES

Tip Temperature Range 1000-1050°F

| w/o Tip | w/ Tip | Tip Diameter | Wattage |
|---------|--------|--------------|---------|
| 92204   | 92206  | 1/8"         | 20      |
| 92254   | 92256  | 1/8"         | 25      |
| 92304   | 92306  | 1/8"         | 30      |
| 92354   | 92356  | 1/8"         | 35      |
| 92404   | 92406  | 1/8"         | 40      |
| 92454   | 92456  | 1/8"         | 45      |
| 92504   | 92506  | 1/8"         | 50      |

| w/o Tip | w/ Tip | Tip Diameter | Wattage |
|---------|--------|--------------|---------|
| 93254   | 93256  | 3/16"        | 25      |
| 93304   | 93306  | 3/16"        | 30      |
| 93354   | 93356  | 3/16"        | 35      |
| 93404   | 93406  | 3/16"        | 40      |
| 93454   | 93456  | 3/16"        | 45      |
| 93504   | 93506  | 3/16"        | 50      |

| w/o Tip | w/ Tip | Tip Diameter | Wattage |
|---------|--------|--------------|---------|
| 94304   | 94306  | 1/4"         | 30      |
| 94404   | 94406  | 1/4"         | 40      |
| 94504   | 94506  | 1/4"         | 50      |
| 94604   | 94606  | 1/4"         | 60      |

### MID-SERIES

#### 4000 SERIES

Tip Temperature Range 1000-1050°F

| w/o Tip | w/ Tip  | Tip Diameter | Wattage |
|---------|---------|--------------|---------|
| 40604*  | 40606*  | 1/4"         | 60      |
| 40704*  | 40706*  | 1/4"         | 70      |
| 40804** | 40806** | 1/4"         | 80      |
| 41004** | 41006** | 1/4"         | 100     |

\*Use minimum 2 1/4" length tips.

\*\*Use minimum 2 3/4" length tips.

### HEAVY-SERIES

#### 8000 SERIES

Tip Temperature Range 900-1100°F

| w/o Tip | w/ Tip | Tip Diameter | Wattage |
|---------|--------|--------------|---------|
| 81504   | 81506  | 1/2"         | 150     |
| 82004   | 82006  | 1/2"         | 200     |
| 82504   | 82506  | 1/2"         | 250     |

### MID-SERIES

#### 6000 SERIES

Tip Temperature Range 900-1025°F

| w/o Tip | w/ Tip | Tip Diameter | Wattage |
|---------|--------|--------------|---------|
| 61004   | 61006  | 3/8"         | 100     |
| 61304   | 61306  | 3/8"         | 130     |
| 61504   | 61506  | 3/8"         | 150     |
| 62004   | 62006  | 3/8"         | 200     |

Irons ending in 4 without tip

Irons ending in 6 with tip

### HEAVY-SERIES

#### 2900 SERIES

Tip Temperature Range 900-1100°F

| w/o Tip | w/ Tip | Tip Diameter | Wattage |
|---------|--------|--------------|---------|
| 29204   | 29206  | 5/8"         | 200     |
| 29254   | 29256  | 5/8"         | 250     |
| 29304   | 29306  | 5/8"         | 300     |
| 29404   | 29406  | 5/8"         | 400     |

All standard Esico•Triton irons are supplied with 3-conductor cordsets. 2-conductor cordsets are available.



**ESICO•TRITON**  
INTERNATIONAL

P. O. Box 247 2 Esico Lane Deep River, Connecticut 06417-0247  
Phone: 800.526.8661 Fax: 860.526.9524 E-mail: sales@esicotriton.com



## SOLDERING IRONS [INDUSTRIAL OFFSET]



### 4000H SERIES

| w/o Tip  | w/ Tip | Tip Diam. | Wattage |
|----------|--------|-----------|---------|
| 40604H*  | 40606H | 1/4"      | 60      |
| 40704H*  | 40706H | 1/4"      | 70      |
| 40804H** | 40806H | 1/4"      | 80      |
| 41004H** | 41006H | 1/4"      | 100     |

\*Use minimum 2 1/4" length tips.

\*\*Use minimum 2 3/4" length tips.

### 6000H SERIES

| w/o Tip | w/ Tip | Tip Diam. | Wattage |
|---------|--------|-----------|---------|
| 61004H  | 61006H | 3/8"      | 100     |
| 61304H  | 61306H | 3/8"      | 130     |
| 61504H  | 61506H | 3/8"      | 150     |



|                   |             |
|-------------------|-------------|
| Irons ending in 4 | without tip |
|-------------------|-------------|

|                   |          |
|-------------------|----------|
| Irons ending in 6 | with tip |
|-------------------|----------|

### 9000H SERIES

| w/o Tip | w/ Tip | Tip Diam. | Wattage |
|---------|--------|-----------|---------|
| 92204H  | 92206H | 1/8"      | 20      |
| 92254H  | 92256H | 1/8"      | 25      |
| 92304H  | 92306H | 1/8"      | 30      |
| 92354H  | 92356H | 1/8"      | 35      |
| w/o Tip | w/ Tip | Tip Diam. | Wattage |
| 93254H  | 93256H | 3/16"     | 25      |
| 93304H  | 93306H | 3/16"     | 30      |
| 93354H  | 93356H | 3/16"     | 35      |
| 93404H  | 93406H | 3/16"     | 40      |
| 93454H  | 93456H | 3/16"     | 45      |
| 93504H  | 93506H | 1/16"     | 50      |
| w/o Tip | w/ Tip | Tip Diam. | Wattage |
| 94304H  | 94306H | 1/4"      | 30      |
| 94404H  | 94406H | 1/4"      | 40      |
| 94504H  | 94506H | 1/4"      | 50      |
| 94604H  | 94606H | 1/4"      | 60      |

All standard Esico•Triton irons are supplied with 3-conductor cordsets. 2-conductor cordsets are available.

**ESICO•TRITON**

INTERNATIONAL

P. O. Box 247

2 Esico Lane

Deep River, Connecticut 06417-0247

Phone: 800.526.8661 Fax: 860.526.9524 E-mail: [sales@esicotriton.com](mailto:sales@esicotriton.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Esico-Triton:](#)

[A40704H](#) [A29254](#) [353050](#)