

プラスチック防水ハンドル
PLASTIC WATERPROOF HANDLES



AP-140

特 徵 Feature

- 防水タイプ(Oリング・シートパッキン使用)
 - 亜鉛合金がインサートされています。
 - 耐酸・耐絶縁性を必要とする扉に最適
 - 左右兼用型
-
- Waterproof (using O-ring and sheet packing)
 - Zinc alloy is inserted.
 - Suitable for doors that require acid-resistance and insulation.
 - For both left-hand and right-hand use.

- | | |
|-----|--|
| 仕 様 | ●材 質:ABS樹脂
●標 準 色: N7(グレー)
5Y7/1(アイボリー)
●鍵 番 号: 2001
●付 属 品: 大ナット・ビスセット(止め金用)・キー2本 |
| 用 途 | ●隧道用配分電盤 |
| 納 期 | ●標準在庫品 |
| 備 考 | ●ダブルOリングの完全防水タイプも製作致します。
●止め金は646～650ページの中からお選びください。
●マスターシステムの組込みが可能です。お問合せください。
●常温でご使用ください。
●施錠は錠前の構造上、鍵を押しながら回してください。
●本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお要め致します。
●緩み防止剤等、溶剤を使用する際は十分に検証を行ってください。 |

- Specifications
- Material: ABS resin
 - Standard color: N7: Gray. 5Y7/1: Ivory
 - Key No.: 2001
 - Accessories: Two keys, large nut and screws (for stopper plate)


- | | |
|--------------|---|
| Specific use | <ul style="list-style-type: none"> • Tunnel power/distribution boards |
| Remarks | <ul style="list-style-type: none"> • Double-O-ring-fully-waterproof type is available. • Select stopper plate on page 646 to 650. • Incorporating master system is possible. Consult us. • Use this product in normal temperatures. • Due to the structure of the lock, the key must be pushed in as it is turned in order to release the lock. • It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch. • Be sure to test adequately when using a solvent such as thread-locking fluid. |




AP-140-1-1
N7

AP-140-2-1
5Y7/1

≡-No.2001
Key



パネル穴明け寸法
Panel drilling dimensions



商品番号 Product No.			備考 Remarks	L1	L2	W1	W2	□W3	(W4)	(H1)	H2	H3	H4	H5	P	φD1	φD2	φD3	(M)	最大適用板厚 Max. applicable panel thickness	製品質量 (g) Mass	コード Code	単 価 Price	量販価格 数量	Bulk Price 単価 Price
AP-140-1-1-N7		2D/3D	鍵付き With lock	158	7	40	25	10	42	61	9	26	24	6	50	70	25	30	M24	9.5	520	00314	¥2,500	10個～	¥2,400
AP-140-1-1-5Y7/1		2D/3D																				01038		10個～	¥2,400
AP-140-1-2-N7		3D	鍵なし Without lock																			00316	¥1,700	10個～	¥1,632
AP-140-1-2-5Y7/1		3D																				01039		10個～	¥1,632
AP-140-2-1-N7		2D/3D	鍵付き With lock	122	6	32	20	8	32	55	7	31	20	4	40	60	23	27	M22	7	330	00318	¥2,250	20個～	¥2,160
AP-140-2-1-5Y7/1		2D/3D																				01040		20個～	¥2,160
AP-140-2-2-N7		3D	鍵なし Without lock																			00320	¥1,650	20個～	¥1,584
AP-140-2-2-5Y7/1		3D																				01041		20個～	¥1,584

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

A

クレモン

ローラー
縮り

特装密閉
ハンドル

フリーザー
密閉

平面
スイング[®]

ギア式

平面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L-SHAPED HANDLES	L 型 ハンドル
	T 型 ハンドル
	丸型 小型
	押ボタン

取手

つまみ

止め金

ジョイント
リンク

ワイヤ

18.0

TAKIGEN
総合 24

497