






| LOC | DIST | REVISIONS |     |                      |         |     |      |
|-----|------|-----------|-----|----------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION          | DATE    | DWN | APVD |
| FT  | 64   |           | Y   | REV PER OG3C-0162-99 | 17NOV00 | RB  | HW   |

1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED.
- 3

 TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 4

 TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.



|                                        |                     |                    |                                          |                                                                                                                                                                         |
|----------------------------------------|---------------------|--------------------|------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| OBSOLETE                               | TINNED              | PHOS.BRZ. .006 THK | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-641609-5                                                                                                                                                              |
| OBSOLETE                               | <div>3</div>        | PHOS.BRZ. .006 THK | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-641609-4                                                                                                                                                              |
| OBSOLETE                               | TINNED              | PHOS.BRZ. .006 THK | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-641609-3                                                                                                                                                              |
| OBSOLETE                               | <div>3</div>        | BE.CU. .006 THK    | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-641609-2                                                                                                                                                              |
|                                        | TINNED              | BE.CU. .006 THK    | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-641609-1                                                                                                                                                              |
| CONTACT FINISH                         |                     | CONTACT MAT'L      | HOUSING MATERIAL                         | PART NO.                                                                                                                                                                |
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                     | DWN<br>R BROWN     | 09JAN01                                  | <div><div>AMP</div><div>Tyco Electronics Corporation</div><div>Harrisburg, PA 17105</div></div> <div>SOCKET ASSY, DIP, LADDER,<br/>RET LEG, 14 POS, DIPLOMATE™ DL</div> |
| DIMENSIONS:<br>INCHES                  |                     | OK<br>H WYNKOOP    | 28AUG00                                  |                                                                                                                                                                         |
|                                        |                     | APVD<br>H WYNKOOP  | 28AUG00                                  |                                                                                                                                                                         |
|                                        |                     | PRODUCT SPEC       | 108-1066                                 |                                                                                                                                                                         |
|                                        |                     | APPLICATION SPEC   | 114-1049                                 |                                                                                                                                                                         |
| MATERIAL<br>SEE TABLE                  | FINISH<br>SEE TABLE | WEIGHT<br>-        | A1                                       | SIZE<br>CAGE CODE<br>DRAWING NO<br>00779                                                                                                                                |
| CUSTOMER DRAWING                       |                     | SCALE<br>5:1       | SHEET<br>1 OF 1                          | REV<br>Y                                                                                                                                                                |