


## Coaxial Cable Connector 11\_SMA-50-2-5/111\_N

### Description

Straight cable plug

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Outer contact	0.0037 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Bronze	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

### Related Documents

Outline drawing	DOU-00006531
Catalogue drawing	DOU-00006102
Assembly instruction	DOC-0000179309

### Ordering Information

Bulk 100 pcs package	11_SMA-50-2-5/111_NH
Single package	11_SMA-50-2-5/111_NE

### Additional Information

Suitable cables	RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG 174 /U
-----------------	--