


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: XMCOLOR
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.0001 [0.00254]
THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

2. P/N W-701/COLOR
28AWG 19X40 TINNED COPPER
0.047 [1.19] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

3. PERFORMANCE
MAXIMUM CURRENT: 1.0 AMPS
MAXIMUM VOLTAGE: 600 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ± ±		CONTRACT NO.		DESCRIPTION	
				APPROVALS		E-Z-HOOK [®] DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
				DRAWN		MICRO-HOOK (XM) JUMPER	
				APPROVED BY		SIZE CODE IDENT NO. DRAWING NO. REV.	
						A 08505 704XM	
NEXT ASSY		USED ON		FINISH		SCALE 1:1 SHEET 1 OF 1	
				SEE NOTE.			
APPLICATION		DO NOT SCALE DRAWING					