



Product Number: 3-1393210-9

Industrial Relays (General Purpose)



Product Type Features:

Termination Type = Through Hole

Electrical Characteristics:

Contact Current Rating (Amps.) = 30

Coil Resistance (Ω) = 25

Actuating System = DC

Coil Power, Nominal (W) = 1.00

Input Voltage (VDC) = 5

Body Related Features:

Series = T9A

Polarized = No

Contact Related Features:

Mounting Options = PC Board

Enclosure = Sealed

FCC Part 68 Isolation = No

Relay Type = PCB

Contact Material = Silver Cadmium Oxide

Approx. Dimensions (L x W x H) (mm [in]) = 32.50 x 27.40 x 27.90 [1.280 x 1.079 x 1.099]

Wiring Diagram = 1 Form C

Approved Standards = UL Recognized, CSA Component Acceptance, CSA Certified

Configuration Related Features:

Contact Arrangement = 1 Form C, SPDT, 1 C/O

Coil Magnetic System = Monostable

Coil Suppression Diode = Without

Coil Selection Criteria = Nominal Voltage

Coil Latching = Without

LED Indicator = Without

Industry Standards:

RoHS/ELV Compliance = RoHS/Not ELV Compliant

Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C

RoHS/ELV Compliance History = Converted to comply with RoHS not ELV directives

Coil Insulation Classification = UL Class F

Other:

Brand = Potter & Brumfield