

OBSOLETE- USE PS-570Q

Specifications

Resonant Frequency (Hz)	2800 $\pm$ 500
Operating Voltage (Vdc)	5 ~ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	200 at Rated Voltage
Sound Pressure Level Min. (dB)	105 at 100cm at Rated Voltage
Tone/Pulse Rate (Hz)	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Wire	20 AWG
Weight (Grams)	107.2
Options	For other options contact factory

Dimensions: (units: mm)
