









FCIconnect.com

Copyright FCI




SECTION X-X




SECTION Y-Y

| mat'l. code |          |     |          | surface  | tolerance                             | projection | product family           |
|-------------|----------|-----|----------|----------|---------------------------------------|------------|--------------------------|
|             |          |     |          | ISO 1302 | ISO 406                               |            | QUICKIE                  |
|             |          |     |          | ISO 1101 | ISO 1101                              |            |                          |
| ltr         | ecp      | no  | dr       | date     | tolerances unless otherwise specified | INCH/MM    | title                    |
| A           | V41735   | MDF | 12/28/94 | 12/28/94 | .XX±.01/.3                            |            | QUICKIE SHROUD           |
| B           | V50149   | MRC | 2/8/95   | 2/8/95   | .XXX±.005/.13                         |            |                          |
| C           | M06-0282 | AGS | 7/22/06  | 7/22/06  | .XXXX±.0020/.051                      | scale 8:1  |                          |
|             |          |     |          | dr       | M. FETROW                             | 12/28/94   | dwg no                   |
|             |          |     |          | enrg     | M. SMYK                               | 12/28/94   | sheet 1 of 2             |
|             |          |     |          | chr      | M. SMYK                               | 12/28/94   | size                     |
|             |          |     |          | appd     | M. SMYK                               | 12/28/94   | A3                       |
| sheet       | revision | C   | C        |          |                                       |            | type                     |
| index       | sheet    | 1   | 2        |          |                                       |            | Product Customer Drawing |

|           | POS    | DIM L       | DIM M       | DIM N       | DIM P     | STYLE |
|-----------|--------|-------------|-------------|-------------|-----------|-------|
| 66247-001 | 2 X 5  | .690/17.53  | .600/15.24  | .540/13.72  | .130/3.30 | A     |
| -002      | 2 X 7  | .890/22.61  | .800/20.32  | .740/18.80  | .130/3.30 |       |
| -003      | 2 X 8  | .990/25.15  | .900/22.86  | .840/21.34  | .220/5.59 |       |
| -004      | 2 X 10 | 1.190/30.23 | 1.100/27.94 | 1.040/26.42 | .220/5.59 |       |
| -005      | 2 X 13 | 1.490/37.85 | 1.400/35.56 | 1.340/34.04 | .130/3.30 |       |
| -006      | 2 X 17 | 1.890/48.01 | 1.800/45.72 | 1.740/44.20 | .130/3.30 |       |
| -007      | 2 X 20 | 2.190/55.63 | 2.100/53.34 | 2.040/51.82 | .220/5.59 |       |
| -008      | 2 X 25 | 2.690/68.33 | 2.600/66.04 | 2.540/64.52 | .130/3.30 |       |
| -009      | 2 X 30 | 3.190/81.03 | 3.100/78.74 | 3.040/77.22 | .220/5.59 |       |
| -010      | 2 X 12 | 1.390/35.31 | 1.300/33.02 | 1.240/31.50 | .220/5.59 |       |
| -011      | 2 X 15 | 1.690/42.93 | 1.600/40.64 | 1.540/39.12 | .130/3.30 |       |
| -012      | 2 X 22 | 2.390/60.71 | 2.300/58.42 | 2.240/56.90 | .220/5.59 |       |
| -013      | 2 X 18 | UNAVAILABLE |             |             |           |       |
| -014      | 2 X 28 | UNAVAILABLE |             |             |           | A     |
| -015      | 2 X 25 | 2.690/68.33 | 2.600/66.04 | 2.540/64.52 | .130/3.30 | B     |
| 66247-016 | 2 X 32 | UNAVAILABLE |             |             |           | A     |



STYLE A  
SCALE 4:1



STYLE B  
SCALE 4:1

NOTES:

1. MATERIAL: 30% GLASS FILLED POLYESTER, FLAME RETARDANT PER UL 94V-0, COLOR: BLUE.
2. THE FIRST TWO CAVITY POSITIONS AND THE LAST TWO POSITIONS ARE IDENTIFIED BY NUMBER.
3. TRIANGULAR POSITION ONE INDICATOR LOCATED APPROXIMATELY AS SHOWN.
4. CENTER LINES OF .0300/.762 DIAMETER HOLES.
5. CENTER LINES OF .0360/.914 DIAMETER HOLES.
6. ROUND HOLE SIZES ALTERNATE BETWEEN .0300/.762 & .0360/.914 DIAMETER, SEE NOTES 4 & 5.

|             |                |    |      |                     |                                                                     |                       |                               |
|-------------|----------------|----|------|---------------------|---------------------------------------------------------------------|-----------------------|-------------------------------|
| mat'l. code |                |    |      | surface<br>ISO 1302 | tolerance<br>ISO 406<br>ISO 1101                                    | projection<br>INCH/MM | product family<br>QUICKIE     |
| ltr         | ecn            | no | dr   | date                | tolerances unless otherwise specified                               |                       | title                         |
| C           |                |    |      |                     | linear .XX±.01/.3<br>linear .xxx±.005/.13<br>linear .xxx±.0020/.051 | INCH/MM               | QUICKIE SHROUND               |
|             |                |    |      |                     | 0'±2'                                                               | scale 8:1             |                               |
|             |                |    | dr   | M. FETROW           | 12/28/94                                                            | FCI                   | dwg no                        |
|             |                |    | enr  | M. SMYK             | 12/28/94                                                            |                       | sheet2 of 2                   |
|             |                |    | chr  | M. SMYK             | 12/28/94                                                            |                       | size                          |
|             |                |    | appd | M. SMYK             | 12/28/94                                                            |                       | 66247 M.SMYK A3               |
| sheet index | revision sheet |    |      |                     |                                                                     |                       | type Product Customer Drawing |