






M55302/130-38	6.400 [162.56]	64	6.524 [165.71]	6.625 [168.27]	6.950 [176.53]	7.250 [184.15]	195	1-531134-3
M55302/130-26	4.400 [111.76]	44	4.524 [114.91]	4.625 [117.47]	4.950 [125.73]	5.250 [133.35]	135	1-531134-2
M55302/130-44	7.900 [200.66]	79	8.024 [203.81]	8.125 [206.37]	8.450 [214.63]	8.750 [222.25]	240	531134-8
M55302/130-41	6.900 [175.26]	69	7.024 [178.41]	7.125 [180.97]	7.450 [189.23]	7.750 [196.85]	210	531134-7
M55302/130-35	5.900 [149.86]	59	6.024 [153.01]	6.125 [155.57]	6.450 [163.83]	6.750 [171.45]	180	531134-6
M55302/130-32	5.400 [137.16]	54	5.524 [140.31]	5.625 [142.87]	5.950 [151.13]	6.250 [158.75]	165	531134-5
M55302/130-29	4.900 [124.46]	49	5.024 [127.61]	5.125 [130.17]	5.450 [138.43]	5.750 [146.05]	150	531134-4
M55302/130-23	3.900 [99.06]	39	4.024 [102.21]	4.125 [104.77]	4.450 [113.03]	4.750 [120.65]	120	531134-3
M55302/130-20	3.400 [86.36]	34	3.524 [89.51]	3.625 [92.07]	3.950 [100.33]	4.250 [107.95]	105	531134-2
M55302/130-17	2.900 [73.66]	29	3.024 [76.81]	3.125 [79.37]	3.450 [87.63]	3.750 [95.25]	90	531134-1
MILITARY P/N	F	E	D	C	B	A	POSN.	PART NO.

- | | | | | | |
|--|--|--|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN. 8-5-92
T. ALEXANDER
CHK. 11-10-92
W. FOLEY
APVD. D. MILLER 11-10-92 | | tyco
Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105-3608 | |
| DIMENSIONS:
INCHES
 | | TOLERANCES, UNLESS
OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
4 P.L.C. ± .005 [0.13]
ANGLES ± .
FINISH | | NAME
BOX RECEPTACLE ASSY., 100,
3-ROW, .014 X .019 CONTACT TAIL,
.025 OFFSET | |
| MATERIAL
 | | APPLICATION SPEC
WEIGHT — | | SIZE CAGE CODE DRAWING NO
A1 00779 C=531134 | |
| | | CUSTOMER DRAWING | | SCALE 4:1 SHEET 1 of 1 REV F | |