

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010011074

Status:

Active

Overview:

KK®

Description:

5.08mm (.200") Pitch KK® Crimp Terminal Housing, 7 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0087 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Name

Crimp Housings

3001

KK®

KK®

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Temperature Range - Operating

7

Natural

94V-2

Female

No

Nylon

1

Bag

No

0.200 In

5.08 mm

-40°C to +105°C

Electrical

CSA

UL

LR19980

E29179

Solder Process Data

Lead-free Process Capability

Wave Capable (TH only)

Material Info

Old Part Number

3001-07


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-99020-0087

SDE-3001-N-*



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

3001Series

Mates With

3061 , 3003 , 3008

Use With

2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG, 2878

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION