



Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 10A/250VAC, 15A/125VAC
- Contact Resistance: <20mΩ @ 2-4VDC 1A
- Insulation Resistance: > 200MΩ @ 500VDC
- Dielectric Strength: 1500VAC
- Electrical Life: Over 10,00 Cycles

Mechanical Specifications:

- Circuit: SPST, On-Off

Soldering Process:

- Soldering Iron: 60w
Solder: 1.60 RH 50 (SN50%)
Temperature: 350°C
Complete Soldering: 2 Seconds
- Soldering Iron: 40w
Solder: 1.00 RH 64 (SN64%)
Temperature: 250°C
Complete Soldering: 2-3 Seconds

Toggle Switch
10TE006

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

10TE006