



Actual

Catalog Number:	500M
Product ID:	7TAH006100R0017
UPC Number:	78378685526
EAN Number:	05414363142522
Status:	A

Type H - High Strength Split-Bolt Connector, Conductor Range for Equal Main and Tap 500 kcmil-400 kcmil, Conductor Range for Min Tap with One Max Main 2/0 Str

- Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper alloy pressure bar.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper alloy pressure bar.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Bronze Alloy
Color	Metallic

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	1
Inner Dimensions (inches)	3.09x2.03x2.78
Outer Quantity	30
Outer Dimensions (inches)	11.4x11.4x6
Weight Uom	92.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com