

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-65-0115](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 3.96mm Pitch KK® Crimp Terminal 2478, 18-24 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)


Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-08-50 \(PDF\)](#)

General
Product Family Crimp Terminals
Series [2478](#)
Application Power
Crimp Quality Equipment Yes
Overview [KK® Interconnection System](#)
Packaging Alternative [08-65-0114](#) (Reel)
Product Name KK®
UPC 800754227230

Physical
Gender Female
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Gold
Net Weight 0.150/g
Packaging Type Bag
Plating min - Mating 0.381µm
Plating min - Termination 0.381µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.79mm max.
Wire Size AWG 18, 20, 22, 24
Wire Size mm² N/A

Material Info
Old Part Number 2478-3-(555)L

Reference - Drawing Numbers
Product Specification PS-08-50
Sales Drawing SD-2478



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[2478Series](#)

Use With
[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) , [5239](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool	0011030016
Hand Crimper	0638117500