

Laser Label Materials

Brady continues to stock the following laser-printable labels.

Laser Printer Sheets - General ID Label Sheets




Fig. Laser-01




Fig. Laser-02

Diagram	Part Number	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horizontal Repeat C Inch (mm)	Horizontal Margin E Inch (mm)	Top Margin F Inch (mm)	Labels Per Row	Labels Per Sheet	Labels Per Pkg
Laser-02	LAT-26-747-10	Polyester	White	0.250 (6.35)	0.250 (6.35)	0.600 (15.24)	0.875 (22.23)	0.400 (10.16)	26	936	10,000
Laser-02	LAT-1-747-10	Polyester	White	0.300 (7.62)	0.250 (6.35)	0.700 (17.78)	0.875 (22.23)	0.450 (11.43)	22	836	10,000
Laser-01	LAT-2-747-10	Polyester	White	0.375 (9.53)	0.375 (9.53)	0.500 (12.70)	0.875 (22.23)	0.313 (7.95)	16	400	10,000
Laser-01	LAT-45-707-10	Polyester	White	0.500 (12.70)	0.375 (9.53)	0.600 (15.24)	0.875 (22.23)	0.400 (10.16)	13	325	10,000
Laser-01	LAT-25-747-10	Polyester	White	0.500 (12.70)	0.437 (11.10)	0.600 (15.24)	0.875 (22.23)	0.400 (10.16)	13	286	10,000
Laser-01	LAT-46-707-10	Polyester	White	0.500 (12.70)	0.500 (12.70)	0.600 (15.24)	0.875 (22.23)	0.400 (10.16)	13	247	10,000
Laser-01	LAT-40-799-1	Nylon Cloth	White	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	0.875 (22.23)	0.400 (10.16)	13	156	1,000
Laser-01	LAT-40-799-5	Nylon Cloth	White	0.500 (12.70)	0.750 (19.05)	0.600 (15.24)	0.875 (22.23)	0.400 (10.16)	13	156	5,000
Laser-01	LAT-38-799-2.5	Nylon Cloth	White	0.500 (12.70)	1.437 (36.50)	0.600 (15.24)	0.875 (22.23)	0.300 (7.62)	13	78	2,500
Laser-01	LAT-3-410-10	Polyolefin	White	0.650 (16.51)	0.250 (6.35)	0.800 (20.32)	0.875 (22.23)	0.325 (8.26)	10	380	10,000
Laser-01	LAT-3-747-10	Polyester	White	0.650 (16.51)	0.250 (6.35)	0.800 (20.32)	0.875 (22.23)	0.325 (8.26)	10	380	10,000
Laser-01	LAT-29-747-10	Polyester	White	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.875 (22.23)	0.325 (8.26)	10	480	10,000
Laser-01	LAT-29-799-10	Nylon Cloth	White	0.650 (16.51)	0.200 (5.08)	0.800 (20.32)	0.875 (22.23)	0.325 (8.26)	10	480	10,000
Laser-01	LAT-4-410-10	Polyolefin	White	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	8	304	10,000
Laser-01	LAT-4-747-10	Polyester	White	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	8	304	10,000
Laser-01	LAT-5-747-10	Polyester	White	0.800 (20.32)	0.500 (12.70)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	8	152	10,000
Laser-01	LAT-5-759-10	Paper	White	0.800 (20.32)	0.500 (12.70)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	8	152	10,000
Laser-01	LAT-37-799-1	Nylon Cloth	White	0.800 (20.32)	1.437 (36.50)	0.900 (22.86)	0.875 (22.23)	0.300 (7.62)	9	54	1,000
Laser-01	LAT-37-799-2.5	Nylon Cloth	White	0.800 (20.32)	1.437 (36.50)	0.900 (22.86)	0.875 (22.23)	0.300 (7.62)	9	54	2,500
Laser-01	LAT-6-747-10	Polyester	White	1.000 (25.40)	0.250 (6.35)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	266	10,000
Laser-01	LAT-8-707-10	Polyester	White	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	175	10,000
Laser-01	LAT-8-747-10	Polyester	White	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	175	10,000
Laser-01	LAT-8-799-10	Nylon Cloth	White	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	175	10,000
Laser-01	LAT-7-410-10	Polyolefin	White	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	133	10,000
Laser-01	LAT-7-707-10	Polyester	White	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	133	10,000
Laser-01	LAT-7-747-10	Polyester	White	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	133	10,000
Laser-01	LAT-7-799-10	Nylon Cloth	White	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	7	133	10,000
Laser-01	LAT-39-799-1	Nylon Cloth	White	1.000 (25.40)	1.437 (36.50)	1.100 (27.94)	0.875 (22.23)	0.300 (7.62)	7	42	1,000
Laser-01	LAT-39-799-2.5	Nylon Cloth	White	1.000 (25.40)	1.437 (36.50)	1.100 (27.94)	0.875 (22.23)	0.300 (7.62)	7	42	2,500
Laser-01	LAT-9-747-10	Polyester	White	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	5	190	10,000
Laser-01	LAT-9-799-10	Nylon Cloth	White	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	5	190	10,000
Laser-01	LAT-41-707-10	Polyester	White	1.500 (38.10)	0.375 (9.53)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	5	125	10,000
Laser-01	LAT-47-707-10	Polyester	White	1.500 (38.10)	0.500 (12.70)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	5	100	10,000
Laser-01	LAT-10-747-10	Polyester	White	1.875 (47.63)	0.250 (6.35)	2.000 (50.80)	0.875 (22.23)	0.314 (7.98)	4	156	10,000
Laser-01	LAT-11-747-5	Polyester	White	1.875 (47.63)	0.375 (9.53)	2.000 (50.80)	0.875 (22.23)	0.310 (7.87)	4	100	5,000
Laser-01	LAT-13-410-2.5	Polyolefin	White	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	4	44	2,500
Laser-01	LAT-13-747-2.5	Polyester	White	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	4	44	2,500
Laser-01	LAT-13-759-2.5	Paper	White	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	4	44	2,500
Laser-01	LAT-14-747-1.5	Polyester	White	1.875 (47.63)	1.330 (33.78)	2.000 (50.80)	0.834 (21.18)	0.315 (8.00)	4	28	1,500
Laser-01	LAT-31-747-1	Polyester	White	2.000 (50.80)	0.900 (22.86)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	3	30	1,000
Laser-01	LAT-33-707-1	Polyester	White	2.000 (50.80)	1.437 (36.50)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	3	18	1,000
Laser-01	LAT-33-747-1	Polyester	White	2.000 (50.80)	1.437 (36.50)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	3	18	1,000
Laser-01	LAT-21-707-1	Polyester	White	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	3	27	1,000
Laser-01	LAT-21-747-1	Polyester	White	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	3	27	1,000