

HEYCO



Heyco® Original Series-35 Liquid Tight Cordgrips




Pigtail, NPT Hubs

- **Flexible Pigtail™ extender prevents sharp bends and extends cable life.**
- IP 68 rated.
- Widest range of approved cable diameters.
- For use in clearance or threaded holes.
- Acme threads on body prevent skipping and speed installation.
- All nylon construction with TPE sealing gland resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL.)
- Multiple sizes for flexible cord diameters ranging from .069" (1,8 mm) to .709" (18,0 mm).
- We recommend using the fitting with the smallest maximum diameter that will fit your application.
- **Locknuts not included.** For nylon locknut specifications or to order locknuts separately, see page 3-41.
- For Heyco Liquid Tight Threaded Plugs, see page 3-45.
- Consult Heyco for cordgrips molded in other colors.

CABLE DIA. RANGE				PART NO.		DESCRIPTION		PART DIMENSIONS									
Minimum		Maximum		Locknuts Not Included* Black Gray				A Clearance Hole Dia.		B Max. O.A. Length		C Thread Length		D Wrenching Thk.		E Nut Flat Size	
in.	mm.	in.	mm.					in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
.069	1,8	.187	4,7	3474	3475	FLEX RLTF 3/8		.670	17,0	2.97	75,4	.53	13,5	.20	5,1	.75	19,1
.181	4,6	.312	7,9	3254	3255	FLEX LTF 3/8											
.170	4,3	.470	11,9	3251	3252	FLEX LTF 1/2		.875	22,2	4.09	103,9	.62	15,7	.20	5,1	.95	24,1
.230	5,8	.546	13,9	3266	3267	FLEX LLTF 1/2		.875	22,2	4.54	115,3	.62	15,7	.23	5,8	1.05	26,7
.250	6,4	.485	12,3	3462	3463	FLEX RLTF 3/4		1.068	27,1	5.14	130,6	.63	16,0	.23	5,8	1.30	33,0
.450	11,4	.709	18,0	3239	3242	FLEX LTF 3/4											

Standard colors black and gray.

*To order Nylon or Metal Locknuts separately, see pages 3-XX and 3-XX.



SUGGESTED CLEARANCE HOLE FOR NONTHREADED MOUNTING

Quick Specs

Material	Nylon 6/6 w/TPE Sealing Gland
Certifications	- UL Listed under Underwriters' Laboratories File E51579 - Recognized under the Component Program of Underwriters' Laboratories File E51579 - CSA Certified by Canadian Standards Association File 93876C
Flammability Rating	94V-2
Temperature Range	Static -40°F (-40°C) to 239°F (115°C) Dynamic -4°F (-20°C) to 212°F (100°C)
IP Rating	IP 68 (70 PSI, 5 BAR)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3251](#) [3254](#) [3239](#) [3266](#) [3242](#) [3252](#) [3255](#) [3267](#) [3463](#) [3475](#) [3474](#) [3462](#)