



Professionally approved products.

Product Datasheet

HSS TiN Fully Ground Stub Drill

EN





Material: HSS

Standard: DIN1897

Point Angle: 135° split point

Surface: TiN tip coating

Package: 5pcs in a plastic tube

Product Details:

RS Art.No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
7877239	1.0	26	6
7877232	1.5	32	9
7877254	2.0	38	12
7877258	2.5	43	14
7877267	3.0	46	16
7877260	3.3	49	18
7877264	3.5	52	20
7877273	4.0	55	22
7877276	4.2	55	22
7877270	4.5	58	24
7877289	5.0	62	26
7877282	5.5	66	28
7877286	6.0	66	28
7877295	6.5	70	31
7877298	6.8	74	34
7877292	7.0	74	34
7877302	7.5	74	34
7877305	8.0	79	37
7877309	8.5	79	37
7877318	9.0	84	40
7877311	9.5	84	40
7877236	10.0	89	43
7877245	10.2	89	43
7877248	11.0	95	47
7877242	12.0	102	51
7877251	13.0	102	51