


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN 4320: ADDED NOTES 3 & 4	12/16/09	D.CASTRO
H	ECN 5837: ADDED LOGO	11/15/11	D. CASTRO
J	ECN 6176: BECAME PREMIUM CABLE, SHIELDED BEADS	4/15/12	D.FRISIELLO
K	ECN 6186: REMOVED INT. METAL BACKSHELL IN FERR. DESC. ADDED TO HOOD	5/24/12	D. DESJARDIN

MODEL NUMBER	LENGTH	
	FEET	METERS
CTLDVIMM-3	3.0	[.92]
CTLDVIMM-5	5.0	[1.52]
CTLDVIMM-10	10.0	[3.05]
CTLDVIMM-15	15.0	[4.57]




2X MALE DVI-D SINGLE
LINK CONNECTOR
30µm GOLD PLATED CONTACTS

"P1"	WIRE MAP	"P2"
19		19 (GND)
18		18 (LT. GREEN)
17		17 (BLACK)
10		10 (YELLOW)
9		9 (BROWN)
11		11 (GND)
15		15 (BLACK)
14		14 (BROWN)
2		2 (RED)
1		1 (ORANGE)
3		3 (GND)
22		22 (GND)
23		23 (LT. BLUE)
24		24 (WHITE)
16		16 (ORANGE)
7		7 (YELLOW)
6		6 (WHITE)
SHELL		SHELL (SHIELD DRAIN WIRE)

PIN 8 NO CONNECTION

NOTES:

1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	12/7/00		
	CHECKED BY RC	3/2/01	CATEGORY AUDIO/VIDEO	
	APPROVED BY ZW	3/5/01	PRODUCT DESCRIPTION CA DVI-D M/DVI-D M W/FERR	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CTLDVIMM	REV. K
		SCALE: NONE	CAD FILE: CTLDVIMM.SLDDRW	SHEET 1 OF 1