


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	9/12/00	TJC
B	REVISED;ADDED COLOR CODE (ECN 1510)	09/18/0	MCCORMICK
C	ECN 3330: CN RELEASE	5/16/08	D.CASTRO
D	ECN 6792: UPDATED LOGO, DRW FORMAT, PACKAGING, ADDED PANTONE #	4/10/13	D. DESJARDIN



MODEL NUMBER	LENGTH	
	FEET	METERS
DK238MM-1	1.0	0.30
DK238MM-2	2.0	0.61
DK238MM-3	3.0	0.91
DK238MM-6	6.0	1.83
DK238MM-10	10.0	3.05
DK238MM-15	15.0	4.57
DK238MM-20	20.0	6.10
DK238MM-25	25.0	7.62

WIRING MAP		
"P1"	COLOR	"P2"
1	LT. BLUE	1
2	LT. GREEN	2
3	PURPLE	3
4	WHITE	4
5	ORANGE	5
6	YELLOW	6
7	BROWN	7
8	RED	8
SHELL	DRAIN	SHELL

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	8/31/00		
	CHECKED BY DFP	9/7/00	CATEGORY I/O PRODUCTS	
	APPROVED BY RC	9/12/00	PRODUCT DESCRIPTION CBL MD8 MALE/ MD8 MALE	
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. DK238MM	REV. D
	SCALE: NONE	CAD FILE: DK238MM.SLDDRW	SHEET 1 OF 1	