


P625 Product Details



P625
(7-1437393-0)
TE Part Number: 7-1437393-0
 Superseded
 [Add to Part List](#)
[Search for Replacement Parts](#)

NEMA Terminal Blocks

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- 600 Series Block Series
- Terminal Block
- Block Type = Flat Base
- Medium Duty Application
- Contact Type = Tubular Clamp

[View all Features](#) | [Find Similar Products](#)

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: • None Available Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Additional Product Images: • Line Drawing Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Type = Terminal Block • Screw Size = 10-32 Slotted Pan Head Electrical Characteristics: • Voltage Rating (VAC) = 300 • Amperes (Amps.) = 30.0 Body Related Features: • Block Series = 600 Series • Block Type = Flat Base • Mount Style = Direct Mount (Flat Base) • Wire Range (Solid and Stranded)[MCM] (AWG) = 22-10 • Blown Fuse Indicator = Without • Blown Fuse Indicator Type = None • Wire Strip Length (mm [in]) = 8.74 [0.344] Contact Related Features: • Contact Type = Tubular Clamp • Pitch (mm [in]) = 9.53 [0.375]	Housing Related Features: • Housing Material = Polypropylene Industry Standards: • RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance • Lead Free Solder Processes = Not reviewed for lead free solder process Operation/Application: • Application = Medium Duty Packaging Related Features: • Terminals Per Foot = 30 Other: • Brand = Buchanan