

3/8"



ITX 30 B Screwdriver bit socket

for recessed TORX® head screws with pilot

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip.

Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

® = reg. trademark of Camcar-Textron Inc. USA

Code	No.	M	mm	L	t	Bore	
1440969	ITX 30 B T20	M 4 - M 5	3,86	49	17	1,55 x 1,86	47
1440977	ITX 30 B T25	M 4,5 - M 5	4,43	49	17	1,93 x 2,04	47
1440985	ITX 30 B T27	M 4,5 - M 6	4,99	49	17	2,18 x 2,29	46
1440993	ITX 30 B T30	M 6 - M 7	5,52	49	17	2,56 x 2,92	84
1429701	ITX 30 B T40	M 7 - M 8	6,65	49	17	2,92 x 3,28	64
1441000	ITX 30 B T45	M 8 - M 10	7,82	49	17	3,45 x 3,68	65
1441019	ITX 30 B T50	M 10	8,83	49	17	3,83 x 3,78	77

3/8"



IS 30 Screwdriver bit socket

for slotted head screws

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip.

Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

Code	No.	mm	mm	L mm		
6666100	IS 30 5,5x1	1,0	5,5	55	27	45
6666290	IS 30 8x1,2	1,2	8,0	55	27	50
6666370	IS 30 10x1,6	1,6	10,0	55	23	55

3/8"



IKS 30 Screwdriver bit socket

for cruciform head screws PHILLIPS

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip.

Chrome-plated, bit as per DIN ISO 8764-1 PH, in GEDORE vanadium special steel, gun-metal finish.

Code	No.	L mm		
6666610	IKS 30 1	55	27	35
6666880	IKS 30 2	55	23	45
6666960	IKS 30 3	55	23	50

DIN 7422

3/8"



IN 30 Screwdriver bit socket

for hexagon head screws

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip.

Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

Code	No.	mm	L	d	t	
6241010	IN 30 4	4	47	17,5	19	43
6241280	IN 30 5	5	47	17,5	19	44
6241360	IN 30 6	6	47	17,5	19	45
6241440	IN 30 8	8	49	17,5	17	47
6242920	IN 30 10	10	49	19,0	17	60