

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0847290002

Status:

Active

Overview:

Sealed Industrial USB Solutions

Description:

Sealed Industrial USB 2.0 Type A Receptacle-to-Pigtail, Neoprene Gasket, 20 AWG, 0.152M Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	84729
Assembly Configuration	Single Ended Connector
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-Pigtail
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	78172504392
Physical	
Cable Length	0.152m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	PBT
Number of Rows	1
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Single Ended	Yes
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Size AWG	20
Wire/Cable Type	USB
Electrical	
Current - Maximum per Contact	1.0A
Impedance	90Ω
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-84729-005-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

84729 Series

Mates With

Industry Standard Bayonet Locking USB
Type A Plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION