

20 Watts

WE Series



- High Power Density
- Fully Regulated Outputs
- Efficiency to 86%
- Low Voltage Outputs
- Remote On/Off
- 2:1 Input Range
- 2.5, 3.3 & 5 V Versions

Specification

Input

Input Voltage Range	• 24 V (18-36 VDC) • 48 V (36-72 VDC)
Input Current	• See table
Input Filter	• Pi network
Undervoltage Lockout	• Turn On > 62% nominal input • Turn Off < 61% nominal input

Output

Output Voltage	• 2.5, 3.3, 5 V single
Output Voltage Adjustment	• $\pm 10\%$
Minimum Load	• 10%
Line Regulation	• $\pm 0.2\%$ max
Load Regulation	• $\pm 1.0\%$ max for 25% to 100% load change
Transient Response	• <500 μs for a 25% step load change
Ripple & Noise	• 75mV pk-pk max, 20MHz BW
Overcurrent Protection	• 110-140% of nominal
Short Circuit Protection	• Continuous
Temperature Coefficient	• ± 0.02 /°C max
Remote On/Off	• On > 5.5 VDC or open circuit • Off < 1.8 VDC, control common referenced to -Vin

General

Efficiency	• See table
Isolation	• 500 VDC Input to Output
Switching Frequency	• 500 kHz typical
MTBF	• 1,500 kHrs to MIL-HDBK-217F

Environmental

Operating Temperature	• -40 °C to +70 °C
Case Temperature	• +100 °C max
Storage Temperature	• -40 °C to +100 °C
EMI/RFI	• Six-sided continuous shield

EMC & Safety

Emissions	• EN55022, level A Conducted • EN55022, level A Radiated
ESD Immunity	• EN61000-4-2, level 2 • Perf Criteria A
Radiated Immunity	• EN61000-4-3 3 V/m • Perf Criteria A
Conducted Immunity	• EN61000-4-6 3 V rms • Perf Criteria A

WE Series

Input Voltage ⁽¹⁾	Output Voltage	Output Current	Input Current ⁽²⁾		Efficiency	Model Number
			No Load	Full Load		
18-36 VDC	2.5 VDC	5000 mA	35 mA	645 mA	81%	WE320
	3.3 VDC	5000 mA	45 mA	828 mA	83%	WE300
	5.0 VDC	4000 mA	45 mA	981 mA	84%	WE301
36-72 VDC	2.5 VDC	5000 mA	25 mA	318 mA	82%	WE420
	3.3 VDC	5000 mA	35 mA	410 mA	84%	WE400
	5.0 VDC	4000 mA	35 mA	485 mA	86%	WE401

1. Nominal input voltage is 24 VDC for WE3xx model numbers and 48 VDC for WE4xx model numbers.
2. Input current is at nominal input voltage.