

(1,27mm) .050"

ISDF, TSDF SERIES


ISDF-07-D-M



T1M44-L-2830-01-G



TSDF-10-D-S



CC03L-2830-01-G

DISCRETE WIRE HOUSINGS & CONTACTS

Mates with:
TFM, TFC

SPECIFICATIONS

For complete specifications
see www.samtec.com?ISDF

Insulator Material:
Black LCP

Contact Material:
BeCu

Plating:
Au over 50µ" (1,27µm) Ni

Operating Temp Range:
-55°C to +80°C (PVC)

-55°C to +125°C (*Teflon®)

Voltage Rating:
275 VAC (PVC)

235 VAC (*Teflon®)

Wire: 28 or 30 AWG

RoHS Compliant: Yes



HAND TOOLS

28 to 30 AWG:

CAT-HT-203-2832-11

*Teflon® is a trademark
of Dupont.

Note: Some lengths, styles
and options are non-standard,
non-returnable.



Mates with:
SFM, SFC

SPECIFICATIONS

For complete specifications
see www.samtec.com?TSDF

Insulator Material:
Black LCP

Contact Material:
BeCu

Plating:
Au over 50µ" (1,27µm) Ni

Operating Temp Range:
-55°C to +80°C (PVC)

-55°C to +125°C (*Teflon®)

Wire:
28 or 30 AWG



RoHS Compliant: Yes

APPLICATION SPECIFIC OPTION

- Color coded cable available (*Teflon® N/A)
- Other plating available
Call Samtec.

*Teflon® is a trademark
of Dupont.

Note: For wiring option
information refer to drawing
on web.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM