

A57 Euro Dual Cord 30VA Transformer Series

Features

- 230 VAC Input
- Euro Dual Cord Style
- Rated for Continuous Duty
- AC outputs up to 30VA
- Meets Safety Agency Requirements
- Complies with EMI/RFI Regulations
- CE Compliant
- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- 1 Year Warranty
- Modified and Custom Designs Also Available
- Manufactured in China

Ault Model	Rated Output Volts AC	Maximum Current-Amps	Maximum VA
A57-065000-K000G	6	5.00	30.0
A57-074286-K000G	7	4.29	30.0
A57-083750-K000G	8	3.75	30.0
A57-093333-K000G	9	3.33	30.0
A57-103000-K000G	10	3.00	30.0
A57-112727-K000G	11	2.73	30.0
A57-122500-K000G	12	2.50	30.0
A57-142143-K000G	14	2.14	30.0
A57-152000-K000G	15	2.00	30.0
A57-161875-K000G	16	1.88	30.0
A57-181666-K000G	18	1.66	30.0
A57-201500-K000G	20	1.50	30.0
A57-221364-K000G	22	1.36	30.0
A57-241250-K000G	24	1.25	30.0

Input

- Voltage 230 VAC
- Line Frequency 50 Hz
- Connector Euro Dual Cord, No Ground

Electrical

- Topology Step Down AC/AC Transformer
- Dielectric Withstand 3000 VAC primary-secondary
1500 VAC primary-core
500 VAC secondary-core
- Protection Current, Thermal or Energy Limiting
- EMI Complies with EMC Directives
- CE CE Compliant

Safety Approvals

- Safety Agencies TUV EN60950

Environmental

- Operating Temperature 0° to 40° C with no derating
- Storage Temperature -30° to +85° C
- Relative Humidity 5% to 95% non-condensing
- Altitude 0-10,000 feet
- Cooling Convectional - non vented case

Mechanical

- Case Dimensions A57 - Euro Dual Cord
3.5 L x 2.6 W x 2.2 H (in)
89 L x 67 W x 55 H (mm)
- Case Material Black 94 V1 Polycarbonate
- Weight 30 ounces, 850 grams,
(excluding cord)
- Cord and Connector 6 ft., 2 Conductor, 18-20 AWG
Ault #3 Connector
Other Connectors Available

ONE YEAR WARRANTY

Ault Incorporated, 7105 Northland Terrace, Minneapolis, MN 55428

Contact Ault Inc. for all your custom design requirements. Phone: 763.592.1900 · Fax 763.592.1911

