














NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO SHEET 1.
2. PACKAGE SPECIFICATION FOR WITH FLANGE REFER TO PK-47151-002.

REVISE NOTE		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: S2014-0536		DRAWN BY		mm		MM ONLY		NTS		METRIC		DATE	
2013/12/05		RZHANG		± ---		DRAWN BY		DATE		TITLE		DATE	
2013/12/17		GRMA		± ---		CHECKED BY		DATE		1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN)		DATE	
2013/12/20		YTYAP		± 0.25		APPROVED BY		DATE		LEAD FREE		DATE	
				± 0.25		MATERIAL NO.				molex			
				±		SEE SHEET 6				DOCUMENT NO.		SHEET NO.	
				ANGULAR ± 3 °		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				SD-47151-001		2 OF 8	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

WITH BACK COVER










NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-0001.
2. PACKAGE SPECIFICATION FOR WITHOUT FLANGE REFER TO PK-47151-001.

REVISE NOTE EC NO: S2014-0536 DRWN:FC00 CHKD:JIAN02 APPR:KHLIM	2013/12/05 2013/12/17 2013/12/20	DESCRIPTION	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm inch		DRAWN BY RZHANG	DATE THIS SHEET ONLY FOR 47151-1061/1071/1081	1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex			
				4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.25 ± --- 1 PLACE ± 0.25 ± --- 0 PLACE ± ±		CHECKED BY GRMA	DATE 2004/07/20				
				ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPROVED BY YTYAP	DATE 2004/07/20				
REV	L1					MATERIAL NO. SEE SHEET 6		DOCUMENT NO. SD-47151-001		SHEET NO. 3 OF 8	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											

10 9 8 7 6 5 4 3 2 1

WITH BACK COVER



THIS IS ONLY FOR
47151-1025/1075/1085/6022/6032/1026/2062

NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-0002.
2. PACKAGE SPECIFICATION FOR WITH FLANGE:
OPTION 1: 47151-1026/2062/6032 REFER TO PK-47151-005,
OPTION 2: 47151-1102 REFER TO PK-47151-003,
OPTION 3: OTHER PART NUMBER REFER TO PK-47151-002.

REVISE NOTE		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
REV		DESCRIPTION				MM ONLY		NTS		METRIC			
L1		REV				DRAWN BY		DATE		TITLE			
						3 PLACES		2004/07/20		1.0 HDMI RIGHT ANGLE			
						2 PLACES		2004/07/20		HEADER ASSEMBLY(19 PIN)			
						1 PLACE		2004/07/20		LEAD FREE			
						0 PLACE		2004/07/20		molex			
						ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
						DRAFT WHERE APPLICABLE		SEE SHEET 6		SD-47151-001		4 OF 8	
						MUST REMAIN		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX					
						WITHIN DIMENSIONS		INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

10

9

8

7

6


5

4





3

2

1



WITHOUT TOP HOLE



NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-1102.
2. PACKAGE SPECIFICATION FOR WITH FLANGE REFER TO PK-47151-002.

REV	DESCRIPTION	REVISE NOTE		
		EC NO:	DATE	BY
L1		S2014-0536	2013/12/05	DRWN:CS00
			2013/12/17	CHKD:JTAN02
			2013/12/20	APPR:KHLIM

QUALITY SYMBOLS
$\nabla_A = 0$
$\nabla_C = 0$
$\nabla_D = 0$

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± 0.25	± 0.010
3 PLACES	± 0.25	± 0.010
2 PLACES	± 0.25	± 0.010
1 PLACE	± 0.25	± 0.010
0 PLACE	± 0.25	± 0.010
ANGULAR $\pm 3^\circ$		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
RZHANG	2004/07/20
CHECKED BY	DATE
GRMA	2004/07/20
APPROVED BY	DATE
YTYAP	2004/07/20
MATERIAL NO.	
SEE SHEET 6	

SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
TITLE		
1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE		
molex		
DOCUMENT NO. SD-47151-001		SHEET NO. 5 OF 8

9

8

7

6

5

4

3

2

1

F

E

D

C

B

A

F

E

D

C

B

A

ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR				
47151-1001	1.80	2.20	/	/	/	W/O	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 3
47151-1041											SEE NOTE 2 (2)		
47151-1051											SEE NOTE 2 (3)		
47151-1003											SEE NOTE 2 (4)		
47151-1061									WITH	BLACK	SEE NOTE 2 (1)		
47151-1071											SEE NOTE 2 (2)		
47151-1081											SEE NOTE 2 (3)		
47151-1011											SEE NOTE 2 (1)		
47151-1211									W/O	NATURE	SEE NOTE 2 (2)		
47151-1311											SEE NOTE 2 (3)		
47151-1021											SEE NOTE 2 (1)		
47151-1091											SEE NOTE 2 (3)		
47151-1031											SEE NOTE 2 (1)		
47151-1101	1.45	1.45	/	/	/	W/O	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	
47151-1141											SEE NOTE 2 (2)		
47151-1151											SEE NOTE 2 (3)		
47151-1111											SEE NOTE 2 (1)		
47151-1161										NATURE	SEE NOTE 2 (2)		
47151-1171											SEE NOTE 2 (3)		
47151-1121											SEE NOTE 2 (1)		
47151-1131											SEE NOTE 2 (1)		
47151-7102	1.45	1.45	M3.0x0.5	16.08	13.38	WITH	WITH	W/O	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 5
47151-7142											SEE NOTE 2 (2)		
47151-7162											SEE NOTE 2 (3)		

REVISE NOTE

EC NO: S2014-0536

2013/12/05

DRWN:FC500

2013/12/17

CHKD:JTAN02

2013/12/20

APPR:KHLIM

2013/12/20

DESCRIPTION

REV

L1

QUALITY SYMBOLS

$\nabla_A=0$

$\nabla_G=0$

$\nabla_P=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.25	± ---
1 PLACE	± 0.25	± ---
0 PLACE	±	±

ANGULAR ± 3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY	DATE
RZHANG	2004/07/20
CHECKED BY	DATE
GRMA	2004/07/20
APPROVED BY	DATE
YTYAP	2004/07/20

MATERIAL NO.

SEE SHEET 6

SIZE

A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

NTS

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

1.0 HDMI RIGHT ANGLE
HEADER ASSEMBLY(19 PIN)
LEAD FREE

molex

DOCUMENT NO.

SD-47151-001

SHEET NO.

7 OF 8

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																														
F	<table><tr><th rowspan="2">ASSEMBLY P/N</th><th colspan="5">DIMENSION</th><th colspan="4">FEATURE</th><th rowspan="2">HOUSING COLOUR</th><th rowspan="2">GOLD PLATING IN CONACT AREA</th><th rowspan="2">SHELL PLATING</th><th rowspan="2">REMARK</th></tr><tr><th>DIM A</th><th>DIM B</th><th>DIM C</th><th>DIM D</th><th>DIM E</th><th>FLANGE</th><th>BACK COVER</th><th>TOP HOLES</th><th>MYLAR</th></tr><tr><td>47151-1002</td><td rowspan="10">1.80</td><td rowspan="10">2.20</td><td rowspan="10">M3.0X0.5</td><td rowspan="10">16.08</td><td rowspan="10">13.38</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="4">W/O</td><td rowspan="4">BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="10">SEE NOTE 2 (a)</td><td rowspan="10">FOR SHEET 4</td></tr><tr><td>47151-1042</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1052</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1062</td><td>SEE NOTE 2 (4)</td></tr><tr><td>47151-2062</td><td rowspan="2">WITH</td><td rowspan="2">BLACK</td><td>SEE NOTE 2 (4)</td></tr><tr><td>47151-1012</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1072</td><td rowspan="4">W/O</td><td rowspan="2">NATURE</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1082</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1022</td><td rowspan="2">BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1032</td><td>NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1102</td><td rowspan="10">1.45</td><td rowspan="10">1.45</td><td rowspan="10">M3.0X0.5</td><td rowspan="10">16.08</td><td rowspan="10">13.38</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="4">W/O</td><td rowspan="4">BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="10">SEE NOTE 2 (a)</td></tr><tr><td>47151-1142</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1152</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1112</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1162</td><td rowspan="4">NATURE</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1172</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1122</td><td rowspan="2">BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1132</td><td>NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1005</td><td rowspan="10">1.80</td><td rowspan="10">2.20</td><td rowspan="10">4-40</td><td rowspan="10">16.08</td><td rowspan="10">13.38</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="6">W/O</td><td rowspan="3">BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="10">SEE NOTE 2 (a)</td></tr><tr><td>47151-1045</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1065</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1015</td><td rowspan="3">NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1035</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1055</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1025</td><td rowspan="4">WITH</td><td rowspan="4">BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1075</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1085</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1026</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6012</td><td rowspan="10">1.80</td><td rowspan="5">2.20</td><td rowspan="10">M3.0X0.5</td><td rowspan="10">14.25</td><td rowspan="10">11.28</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="10">WITH</td><td rowspan="3">W/O</td><td rowspan="3">BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="10">SEE NOTE 2 (a)</td></tr><tr><td>47151-6042</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-6052</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-6022</td><td rowspan="3">WITH</td><td rowspan="3">BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6032</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-6112</td><td rowspan="5">W/O</td><td rowspan="5">BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6142</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-6152</td><td>SEE NOTE 2 (3)</td></tr></table>											ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR	47151-1002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 4	47151-1042	SEE NOTE 2 (2)	47151-1052	SEE NOTE 2 (3)	47151-1062	SEE NOTE 2 (4)	47151-2062	WITH	BLACK	SEE NOTE 2 (4)	47151-1012	SEE NOTE 2 (1)	47151-1072	W/O	NATURE	SEE NOTE 2 (2)	47151-1082	SEE NOTE 2 (3)	47151-1022	BLACK	SEE NOTE 2 (1)	47151-1032	NATURE	SEE NOTE 2 (1)	47151-1102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-1142	SEE NOTE 2 (2)	47151-1152	SEE NOTE 2 (3)	47151-1112	SEE NOTE 2 (1)	47151-1162	NATURE	SEE NOTE 2 (2)	47151-1172	SEE NOTE 2 (3)	47151-1122	BLACK	SEE NOTE 2 (1)	47151-1132	NATURE	SEE NOTE 2 (1)	47151-1005	1.80	2.20	4-40	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-1045	SEE NOTE 2 (2)	47151-1065	SEE NOTE 2 (3)	47151-1015	NATURE	SEE NOTE 2 (1)	47151-1035	SEE NOTE 2 (2)	47151-1055	SEE NOTE 2 (3)	47151-1025	WITH	BLACK	SEE NOTE 2 (1)	47151-1075	SEE NOTE 2 (2)	47151-1085	SEE NOTE 2 (3)	47151-1026	SEE NOTE 2 (1)	47151-6012	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-6042	SEE NOTE 2 (2)	47151-6052	SEE NOTE 2 (3)	47151-6022	WITH	BLACK	SEE NOTE 2 (1)	47151-6032	SEE NOTE 2 (3)	47151-6112	W/O	BLACK	SEE NOTE 2 (1)	47151-6142	SEE NOTE 2 (2)	47151-6152	SEE NOTE 2 (3)	F
ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA		SHELL PLATING	REMARK																																																																																																																																																										
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR																																																																																																																																																															
47151-1002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 4																																																																																																																																																											
47151-1042											SEE NOTE 2 (2)																																																																																																																																																													
47151-1052											SEE NOTE 2 (3)																																																																																																																																																													
47151-1062											SEE NOTE 2 (4)																																																																																																																																																													
47151-2062									WITH	BLACK	SEE NOTE 2 (4)																																																																																																																																																													
47151-1012											SEE NOTE 2 (1)																																																																																																																																																													
47151-1072									W/O	NATURE	SEE NOTE 2 (2)																																																																																																																																																													
47151-1082											SEE NOTE 2 (3)																																																																																																																																																													
47151-1022										BLACK	SEE NOTE 2 (1)																																																																																																																																																													
47151-1032											NATURE			SEE NOTE 2 (1)																																																																																																																																																										
47151-1102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																												
47151-1142											SEE NOTE 2 (2)																																																																																																																																																													
47151-1152											SEE NOTE 2 (3)																																																																																																																																																													
47151-1112											SEE NOTE 2 (1)																																																																																																																																																													
47151-1162									NATURE	SEE NOTE 2 (2)																																																																																																																																																														
47151-1172										SEE NOTE 2 (3)																																																																																																																																																														
47151-1122										BLACK	SEE NOTE 2 (1)																																																																																																																																																													
47151-1132											NATURE		SEE NOTE 2 (1)																																																																																																																																																											
47151-1005									1.80	2.20	4-40		16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																			
47151-1045																				SEE NOTE 2 (2)																																																																																																																																																				
47151-1065	SEE NOTE 2 (3)																																																																																																																																																																							
47151-1015	NATURE	SEE NOTE 2 (1)																																																																																																																																																																						
47151-1035		SEE NOTE 2 (2)																																																																																																																																																																						
47151-1055		SEE NOTE 2 (3)																																																																																																																																																																						
47151-1025	WITH	BLACK	SEE NOTE 2 (1)																																																																																																																																																																					
47151-1075			SEE NOTE 2 (2)																																																																																																																																																																					
47151-1085			SEE NOTE 2 (3)																																																																																																																																																																					
47151-1026			SEE NOTE 2 (1)																																																																																																																																																																					
47151-6012	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																												
47151-6042											SEE NOTE 2 (2)																																																																																																																																																													
47151-6052											SEE NOTE 2 (3)																																																																																																																																																													
47151-6022									WITH	BLACK	SEE NOTE 2 (1)																																																																																																																																																													
47151-6032											SEE NOTE 2 (3)																																																																																																																																																													
47151-6112		W/O									BLACK		SEE NOTE 2 (1)																																																																																																																																																											
47151-6142									SEE NOTE 2 (2)																																																																																																																																																															
47151-6152									SEE NOTE 2 (3)																																																																																																																																																															
E																				E																																																																																																																																																				
D																				D																																																																																																																																																				
C												C																																																																																																																																																												
B												B																																																																																																																																																												
A	<table><tr><td rowspan="10">REVISE NOTE EC NO: S2014-0536 DRWN:FC500 2013/12/05 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20</td><td rowspan="10">QUALITY SYMBOLS F=0 F=0 F=0</td><td rowspan="10">DESCRIPTION REV</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="5">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="5">± --- ± --- ± 0.25 ± 0.25 ±</td><td rowspan="5">± --- ± --- ± --- ± --- ±</td><td>DRAWN BY RZHANG</td><td>DATE 2004/07/20</td><td rowspan="5">TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE</td></tr><tr><td>CHECKED BY GRMA</td><td>DATE 2004/07/20</td></tr><tr><td>APPROVED BY YTYAP</td><td>DATE 2004/07/20</td></tr><tr><td colspan="2">MATERIAL NO. SEE SHEET 6</td><td>DOCUMENT NO. SD-47151-001</td><td>SHEET NO. 8 OF 8</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>											REVISE NOTE EC NO: S2014-0536 DRWN:FC500 2013/12/05 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20	QUALITY SYMBOLS F=0 F=0 F=0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.25 ± 0.25 ±	± --- ± --- ± --- ± --- ±	DRAWN BY RZHANG	DATE 2004/07/20	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE	CHECKED BY GRMA	DATE 2004/07/20	APPROVED BY YTYAP	DATE 2004/07/20	MATERIAL NO. SEE SHEET 6		DOCUMENT NO. SD-47151-001	SHEET NO. 8 OF 8	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		A																																																																																																																													
REVISE NOTE EC NO: S2014-0536 DRWN:FC500 2013/12/05 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20	QUALITY SYMBOLS F=0 F=0 F=0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																																															
			4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.25 ± 0.25 ±	± --- ± --- ± --- ± --- ±	DRAWN BY RZHANG	DATE 2004/07/20	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE																																																																																																																																																																
						CHECKED BY GRMA	DATE 2004/07/20																																																																																																																																																																	
						APPROVED BY YTYAP	DATE 2004/07/20																																																																																																																																																																	
						MATERIAL NO. SEE SHEET 6			DOCUMENT NO. SD-47151-001	SHEET NO. 8 OF 8																																																																																																																																																														
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																														
			tb_frame_A3_P_AM.T Rev. G 2012/01/11	9	8	7	6	5	4	3	2				1																																																																																																																																																									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[47151-1022](#)