

BULK WIRE & CABLE



FIG. 1

CAT5e 350MHZ UTP SOLID/STRANDED UTP

- Meets Category 5e requirements as per ANSI/TIA/EIA, ISO/IEC standards
- 2nd Edition ISO/IEC 11801 CAT5e
- Excellent ACR values for Power Sum NEXT/ELFEXT attenuation and return loss
- UL Listed type CM/CMH
- PVC Jacket
- 350MHz Rated cable
- 4 pair 24AWG Solid or stranded copper
- 1,000 Foot pull-boxes



FIG. 2

CAT6 FUTURE LAN 550 SOLID UTP

- Exceeds CAT-6 Standards per EIA/TIA CAT-6 specifications
- Positive ACR @ 250Mhz
- UL Listed type CM/CMR
- PVC Jacket
- 4 pair 23AWG Solid copper
- 1,000 Foot pull-boxes

FIG. 3



FIG. 4



SOLID CAT5e CABLE

ITEM#	DESCRIPTION	FIGURE
NBW-1051	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE-BLACK	1
NBW-1052	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE-BLUE	1
NBW-1053	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE- RED	1
NBW-1054	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE-ORANGE	1
NBW-1055	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE-YELLOW	1
NBW-1056	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE- GREEN	1
NBW-1058	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE- WHITE	1
NBW-1059	4P CAT5e 350 MHZ 24 AWG SOLID UTP CABLE-GRAY	1

STRANDED CAT5e CABLE

ITEM#	DESCRIPTION	FIGURE
NBW-1151	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE-BLACK	1
NBW-1152	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE-BLUE	1
NBW-1153	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE- RED	1
NBW-1154	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE-ORANGE	1
NBW-1155	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE-YELLOW	1
NBW-1156	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE- GREEN	1
NBW-1158	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE- WHITE	1
NBW-1159	4P CAT5e 350 MHZ 24 AWG STRANDED UTP CABLE-GRAY	1

SOLID CAT6 CABLE

ITEM#	DESCRIPTION	FIGURE
NBW-1062	CAT 6 SOLID UTP CABLE- BLUE	2
NBW-1069	CAT 6 SOLID UTP CABLE- GRAY	2
NBW-1068	CAT 6 SOLID UTP CABLE- WHITE	2

SOLID & STRANDED VOICE GRADE CABLE

ITEM#	DESCRIPTION	FIGURE
NBW-2428	4C 28AWG SILVER SATIN FLAT - 1,000 FT	3
NBW-2628	6C 28AWG SILVER SATIN FLAT - 1,000 FT	3
NBW-2828	8C 28AWG SILVER SATIN FLAT - 1,000 FT	3
NBW-1426	2PR.(4C) 24AWG ROUND SOLID - 1,000 FT	4
NBW-1626	3PR.(6C) 24AWG ROUND SOLID - 1,000 FT	4
NBW-1826	4PR.(8C) 24AWG ROUND SOLID - 1,000 FT	4

*See page 55 for other wire products.